

2N6052

Silicon PNP Transistors Darlington Power Amplifier TO-3 Type Package

Description:

The 2N6052 is a silicon PNP Darlington transistor in a TO-3 type case designed for general-purpose amplifier and low-frequency switching applications.

Features:

- High DC Current Gain: $h_{FE} = 3500$ Typ @ $I_C = 5A$
- Collector-Emitter Sustaining Voltage: $V_{CEO(sus)} = 100V$ Min @ 100mA
- Monolithic Construction with Built-In Base-Emitter Shunt Resistors

Absolute Maximum Ratings:

Collector-Emitter Voltage, V_{CEO}	100V
Collector-Base Voltage, V_{CB}	100V
Emitter-Base Voltage, V_{EB}	5V
Collector Current, I_C	
Continuous	12A
Peak	20A
Base Current, I_B	200mA
Total Power Dissipation ($T_C = +25^\circ C$), P_D	150W
Derate Above $25^\circ C$	0.857W/ $^\circ C$
Operating Junction Temperature Range, T_J	-65° to $+200^\circ C$
Storage Temperature Range, T_{stg}	-65° to $+200^\circ C$
Thermal Resistance, Junction-to-Case, R_{thJC}	1.17 $^\circ C/W$

Electrical Characteristics: ($T_C = +25^\circ C$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF Characteristics						
Collector-Emitter Sustaining Voltage	$V_{CEO(sus)}$	$I_C = 100mA$, $I_B = 0$, Note 1	100	—	—	V
Collector Cutoff Current	I_{CEO}	$V_{CE} = 50V$, $I_E = 0$	—	—	1.0	mA
	I_{CEX}	$V_{CE} = 100V$, $V_{BE(off)} = 1.5V$	—	—	0.5	mA
		$V_{CE} = 100V$, $V_{BE(off)} = 1.5V$, $T_A = +150^\circ C$	—	—	5.0	mA
Emitter Cutoff Current	I_{EBO}	$V_{BE} = 5V$, $I_C = 0$	—	—	2.0	mA

Note 1. Pulse Test: Pulse Width = 300 μs , Duty Cycle = 2%

Electrical Characteristics (Cont'd): ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
ON Characteristics (Note 1)						
DC Current Gain	h_{FE}	$V_{CE} = 3\text{V}, I_C = 6\text{A}$	750	–	18000	
		$V_{CE} = 3\text{V}, I_C = 12\text{A}$	100	–	–	
Collector–Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 6\text{A}, I_B = 24\text{mA}$	–	–	2.0	V
		$I_C = 12\text{A}, I_B = 120\text{mA}$	–	–	3.0	V
Base–Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 12\text{A}, I_B = 120\text{mA}$	–	–	4.0	V
Base–Emitter ON Voltage	$V_{BE(on)}$	$V_{CE} = 3\text{V}, I_C = 6\text{A}$	–	–	2.8	V
Dynamic Characteristics						
Small–Signal Current Gain	h_{fe}	$V_{CE} = 3\text{V}, I_C = 5\text{A}, f = 1\text{kHz}$	300	–	–	
Magnitude of Common Emitter Small–Signal Short–Circuit Forward Current Transfer Ratio	$ h_{fe} $	$V_{CE} = 3\text{V}, I_C = 5\text{A}, f = 1\text{MHz}$	4.0	–	–	MHz
Output Capacitance	C_{ob}	$V_{CB} = 10\text{V}, I_E = 0, f = 0.1\text{MHz}$	–	–	500	pF

Note 1. Pulse Test: Pulse Width = 300 μs , Duty Cycle = 2%

