

**Features**

- X2 class capacitor RE series with insulated flexible wire leads
- UL, CSA (cUL), IEC/EN 60384-14 (class X2)

Applications


- Industrial machinery, electric appliances and lighting






Safety Standard	File No.*
UL :UL60384-14	E236227
cUL :CSA E60384-14	E236227
ENEC/SEMKO :IEC/EN 60384-14	SE-ENEC-2100337R1

The "ENEC" mark is a common European product certification mark based on testing to harmonised European safety standard. The mark with #14 stands for SEMKO.

* File No. may be revised without notice. Please contact us at the time of your request for certifications.

**Dimensions**

Unit: mm

**Circuit****Model numbering system****Electrical Specifications**Rated Voltage **275Vac**

Safety Standard	Class	Model Number	Capacitance μF±10%	Dimensions (mm)			Dissipation Factor	Test Voltage	Insulation Resistance
				W	H	T			
	X2	REB473	0.047	17.0	12.5	5.5	0.003max. (at 10kHz)	Line to Line 1,250Vac 50/60Hz 60sec	Line to Line C≤0.33μF 15,000MΩmin. Line to Case C≥0.47μF 5,000Ω•Fmin. (at 100Vdc)
		REB683	0.068		13.5	6.5			
		REB104	0.1		15.0	8.0			
		REB154	0.15	20.0	17.5	8.5			
		REB224	0.22						
		REB334	0.33	27.0	18.0	8.0			
		REB474	0.47		19.5	9.5			
		REB684	0.68	32.0	21.5	10.5			
		REB105	1.0		23.5	12.5			

Operating Temperature: -40~+100°C