


DRG. No.

A05-1006

FOR EXPLANATION OF DIMENSIONING, ETC. SEE B.S.308

REMOVE ALL BURRS & SHARP EDGES.

A RADIUS OR CHAMFER .02 (MAX.) IS PERMITTED IN CORNERS OF BLIND HOLES, RECESSES & STEPS.

THIRD ANGLE PROJECTION

4 HOLES $.031$ (0.787) EQUI-SPACED ON
 $.200 \pm .005$ PCD

Part No	Rev No	Material
TOS-006P	TOS-1006P	Al407.

DATE	CHANGES			
29-7-70	A	EQUIV. METRIC DIMS. ADDED.	TOLERANCE ($0, 25$)	DRAWN <i>E.P.</i>
1.3.78	B	Drawn to match TOS-1006P added (21)	± 0.010 max	TRACED
4.1.79	C	CNN ^o 0096.	MATERIAL	CHECKED
				DATE 29 MAY 1966
TITLE			SCALE: 5:1	DRG. No.
MOUNTING PAD TRANSISTOR			DIMS. INCHES (mm)	A05-1006.
JERMYN INDUSTRIES VESTRY ESTATE, OTFORD, NR. SEVENOAKS, KENT.				

H.N.L. 709/64