




Color:  white



Dimensions in mm

Strain relief housing *WINSTA*® MIDI 4-pole

The strain relief housing from the *WINSTA*® MIDI product line guarantees you the greatest flexibility in electrical installation. With WAGO, you benefit from a large selection of accessories for the *WINSTA*® product line. The *WINSTA*® MIDI product line allows maximum flexibility for the installation of applications. With its Push-in CAGE CLAMP® spring pressure connection technology, it ensures error-free, time-saving installation and offers customization and flexibility for meeting all installation requirements. The strip length is 55 mm.

Push-in CAGE CLAMP® spring pressure connection technology – pluggable installation instead of laborious screw connections!

*WINSTA*® is the pluggable connection system that is ideally tailored to the strict requirements of electrical installation. It offers fast, secure and, above all, error-free installation of components and cables. Enjoy the benefits of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismating from WAGO.

- for automation controllers
- quick replacement of defective units during ongoing operation

| Connection data                     |             |
|-------------------------------------|-------------|
| Connection 1                        |             |
| Pole number                         | 4           |
| Connectable sheathed cable diameter | 9 ... 13 mm |
| Strip length (outer insulation)     | 55 mm       |




| Physical data |                        |
|---------------|------------------------|
| Pin spacing   | 10 mm / 0.394 inches   |
| Width         | 44.6 mm / 1.756 inches |
| Height        | 17 mm / 0.669 inches   |
| Depth         | 50 mm / 1.969 inches   |

| Material data                      |                                                                          |
|------------------------------------|--------------------------------------------------------------------------|
| Note (material data)               | <a href="#">Information on material specifications can be found here</a> |
| Color                              | white                                                                    |
| Insulation material (main housing) | Polyamide (PA66)                                                         |
| Flammability class per UL94        | V0                                                                       |
| Fire load                          | 0.326 MJ                                                                 |
| Weight                             | 12.2 g                                                                   |

| Environmental requirements               |                                            |
|------------------------------------------|--------------------------------------------|
| Processing temperature                   | -5 ... +40 °C                              |
| Continuous operating temperature         | -35 ... +85 °C                             |
| Note on continuous operating temperature | Insulating parts for temperatures ≤ 105 °C |

| Commercial data       |               |
|-----------------------|---------------|
| Product Group         | 20 (Winsta)   |
| eCl@ss 10.0           | 27-44-06-92   |
| eCl@ss 9.0            | 27-44-06-92   |
| ETIM 8.0              | EC002863      |
| ETIM 7.0              | EC002863      |
| PU (SPU)              | 25 pcs        |
| Packaging type        | Box           |
| Country of origin     | DE            |
| GTIN                  | 4017332755306 |
| Customs tariff number | 39269097900   |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

| Approvals / Certificates                                                           |          |                  |                                                                                                                                                                          |           |                  |
|------------------------------------------------------------------------------------|----------|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|------------------|
| General approvals                                                                  |          |                  | Approvals for marine applications                                                                                                                                        |           |                  |
|  |          |                  |   |           |                  |
| Approval                                                                           | Standard | Certificate Name | Approval                                                                                                                                                                 | Standard  | Certificate Name |
| cURus<br>Underwriters Laboratories Inc.                                            | UL 1977  | E45171           | DNV GL<br>Det Norske Veritas, Germanischer Lloyd                                                                                                                         | -         | TAE00001Z6       |
| cURus<br>Underwriters Laboratories Inc.                                            | UL 1059  | E 45172          | LR<br>Lloyds Register                                                                                                                                                    | IEC 61984 | LR22429487TA     |



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 770-514

↓

| Documentation |            |     |          |   |
|---------------|------------|-----|----------|---|
| Bid Text      |            |     |          |   |
| 770-514       | 19.02.2019 | xml | 2.73 KB  | ↓ |
| 770-514       | 12.03.2015 | doc | 23.50 KB | ↓ |

CAD/CAE-Data

CAD data

2D/3D Models 770-514

↓

CAE data

EPLAN Data Portal 770-514

↓

WSCAD Universe 770-514

↓

ZUKEN Portal 770-514

↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 210-333

Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive; white