

ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and onsemi. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

Getting Started with Power Line Communication

Introduction

ON Semiconductor has developed a power line communication (PLC) solution for metering and machine-to-machine applications with spread frequency shift keying (S-FSK).

This application note describes how to get started with power line communication using the NCN49597 and NCN49599 modems. It proposes five steps towards an end product: choosing a modem and firmware (sections 1 and 2), selecting an evaluation kit (section 3), building a prototype (section 4) and writing application software (section 5).



ON Semiconductor®

www.onsemi.com

APPLICATION NOTE

Only an overview is given below; detailed information is available in [5, 6, 7, 8].

1 SELECTING A PRODUCT

ON Semiconductor currently offers the NCN49597 and NCN49599 as successors of the highly successful AMIS-49587 PLC modem¹.

Both are single chip half duplex S-FSK modems designed for hostile communication environments with very low signal-to-noise ratio (SNR) and high interference. Together with firmware, they handle the lower layers of communication protocols. Because the lower layers are handled on-chip, the user can concentrate on the higher application layers resulting in faster development.

The NCN49597 and NCN49599 are functionally identical except that the latter integrates a power operational

amplifier (opamp). The opamp can be used as a line driver; it is also available as a separate part, NCS5651, which is recommended for use with the NCN49597.

The NCN49599 is well-suited for cost-sensitive applications; the NCN49597 is recommended for concentrator and multi-phase applications².

The modem communicates with the user over a serial interface. Firmware must be loaded immediately after reset. This may be done over the serial interface; alternatively, the modem can autonomously retrieve the firmware from an attached SPI memory. For more information, refer to [6, "Boot loader"].

2 FIRMWARE

ON Semiconductor offers a royalty-free firmware solution called ON-PL110.

It implements a mesh network topology based on a proprietary extension of the KNX PL110 specification [4]. Typical applications are smart grid home and building automation, solar panel control, lighting and industrial control, and split metering.

The firmware provides both the physical (PHY) layer and media access control (MAC) layer,³ reducing the implementation effort for the user.

The ON-PL110 stack features hierarchical addressing, collision avoidance, error-repairing block coding and dual channel operation. In addition, communication is possible on both AC and DC grids.

¹ This modem and its predecessor, the AMIS-30585, are still available but not preferred for new designs. They can not be reprogrammed and only support the firmware embedded in the integrated read-only memory.

² More information may be found in [5, "Multi-phase designs"].

³ Any layer can be selected as the top layer; the higher layers (if any) are automatically disabled. This allows application tailored protocols.

⁴ In the context of metering applications, the master is a concentrator (or "client" in the IEC terminology) and the slaves are electricity meters ("servers"). Typically, a concentrator controls 100–200 meters.



Figure 1. Contents of a PLC Evaluation Kit



Figure 2. Evaluation Board: Motherboard and Plugged-on Daughterboard

3 SELECTING AN EVALUATION KIT

Evaluation kits (EVKs) are available for the NCN49597 and NCN49599; a kit contains two motherboards and two daughterboards (Figures 1 and 2), allowing the user to set up communication quickly. For more details, refer to [5].

The EVKs are provided in two variants with different receive and transmit filters (Figure 3).




Figure 3. Daughterboard and evaluation kits are available for various frequency ranges. The -1 dB bandwidth of the receive filter is shown in black for each daughterboard, indicating the optimal carrier frequency range. The -10 dB bandwidth is also shown (white).

The first EVK variant is optimised for the widely used IDIS⁵ carrier frequencies (63.3 kHz and 74.5 kHz). In most countries these frequencies are reserved for utility companies; therefore this EVK is available only upon special request.

The second EVK variant covers the B, C and D band, i.e. 95–148.5 kHz (“J” daughterboards).

If you wish to communicate on other frequencies it is recommended to order “D” or “K” daughterboards together with the evaluation kit.

Separately, daughterboards are available covering the CENELEC A band (9–95 kHz; “D” daughterboards), all CENELEC bands (9–148.5 kHz; “K”) and the PL110 frequencies 105 kHz and 115 kHz (“G”).

The usual lead time is three weeks. To receive a quote, please contact your sales representative and specify the orderable part number (OPN) from Table 1 and your preferred distributor. Please also specify your target application so that we can assist you better.

⁵ IDIS is a specification for smart meters defined by the Interoperable Device Interface Specifications (IDIS) Industry Association.

4 BUILDING A PROTOTYPE

Before a final application printed circuit board (PCB) is designed, it usually makes sense to build a prototype. This reduces risk and allows rapid software development and evaluation.

An evaluation board can readily be used as a development platform. During normal operation a computer controls the

modem over a USB connection. However, a user microcontroller can be connected easily, replacing this connection and assuming control (Figure 4). For more information, refer to [5].

Table 1. ORDERABLE PART NUMBERS (OPN) OF THE PLC EVALUATION KITS AND DAUGHTERBOARDS

	Carrier Frequencies [kHz]	Product	
		NCN49597	NCN49599
EVK	E: 63.3 & 74.5 J: 95–150	NCN49597ID11GEVK NCN49597PD11GEVK	NCN49599ID11GEVK NCN49599PD11GEVK
Daughterboard	D: 9–95 K: 9–150 G: 105 & 115	NCN49597DBD1GEVB NCN49597DBK1GEVB NCN49597DBG1GEVB	NCN49599DBG1GEVB NCN49599DBG2GEVB*

*Low-cost variant; 6 weeks lead time; 25 pieces minimum ordering quantity.




Figure 4. Building a Prototype with an EVK

It is also possible to incorporate daughterboards in a prototype. ON Semiconductor can supply tested daughterboards at-cost for low volume pilot deployments, saving considerable development effort and ensuring a short time-to-market.

To reduce cost and board size a low-cost variant of the NCN49599 daughter board is available (NCN49599DBG2GEVB). Refer to [9] for more information. A minimum ordering quantity of 25 applies for this variant.

5 WRITING APPLICATION SOFTWARE

In a typical application, the modem is controlled by an external microcontroller.

ON Semiconductor provides extensive support for developing the firmware of this microcontroller. We can provide documentation demonstrating how to configure the modem by means of management information base (MIB) get and set operations, and how to order the modem to transmit packets.

Reference firmware⁶ for Cortex-M3 microcontrollers will be published in the near future. The source code is easily ported to other microcontrollers.

The modem firmware provides ample support to assess the PLC link quality, including in-band signal statistics reporting. As a result, debugging is simplified and a faster development pace is assured.

Note that the modem firmware is delivered as a binary only; modifying the code and adding application functionality is not possible.

⁶ This implementation is provided without warranty and for illustration purposes only. Contact your sales representative for more information and to obtain a copy of the source code.

REFERENCES

- [1] Électricité réseau distribution France, ERDF. Linky PLC profile functional specification, September 2009. Online at <http://www.erdfdistribution.fr/medias/Linky/ERDF-CPT-Linky-SPEC-FONC-CPL.pdf>, accessed 2014-02-20.
- [2] IEC. Automatisation de la distribution à l'aide de systèmes de communication à courants porteurs – partie 4: Protocoles de communication de données – Section 32: Couche liaison de données – Contrôle de liaison logique (LLC), September 1996.
- [3] IEC. Automatisation de la distribution à l'aide de systèmes de communication à courants porteurs – Partie 5-1: Profils des couches basses, May 2001.
- [4] KNX Association. KNX powerline PL 110 basic course, April 2013.
- [5] ON Semiconductor. Evaluation kit for power-line communication user manual (preview), December 2014.
- [6] ON Semiconductor. NCN49597 power line carrier modem datasheet, December 2014. Online at http://www.onsemi.com/pub_link/Collateral/NCN49597-D.PDF.
- [7] ON Semiconductor. NCN49599 power line carrier modem datasheet, December 2014. Online at http://www.onsemi.com/pub_link/Collateral/NCN49599-D.PDF.
- [8] ON Semiconductor. PLC ESW and EVK selection guide (application note), October 2013.
- [9] Pierre Woestyn and Peter Cox. *PLC evaluation boards enable rapid in-home display prototyping* (application note). ON Semiconductor, April 2016.

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
 USA/Canada
Europe, Middle East and Africa Technical Support:
 Phone: 421 33 790 2910
Japan Customer Focus Center
 Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative