



MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE3-12



.071 MAX
PRETRAVEL

1.122 ± .039
OPERATING
POSITION

2.638 MAX

2X Ø .200 ± .010
MOUNTING HOLES
(Ø .40 C'BORE
.24 DEEP)

.300 ± .010

1.732 MAX

144.000 MIN

P.V.C. SHEATHED CABLE
18/4 S.J.T.O.

.984 ± .010

Ø .48 X .20 WIDE
HARDENED STEEL
ROLLER

.51


NOTES

1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 2.7 LB MAX
RELEASE FORCE — — — — 1.0 LB MIN
DIFFERENTIAL TRAVEL — — — .004 MAX
OVERTRAVEL — — — — — .118 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

5A - 250 VAC
1/10HP - 125 OR 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT

914CE3-12

M

DRAWING
NUMBER

2

ISSUE

REPLACES

RELEASE NO. PR-15896

CHECK

REVISIONS

A CO-
69061
S A V
4 OCT 91

CHECK

DDM/CAD

DRAWN

CHECK

S A V 4 OCT 91