




used for: D-SUB HD

P.C.B. HOLE DRILLINGS

EDGE OF P.C.B.

(b)

4-40 UNC

SEE NOTE 7

NOTES:

1. METALSHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µ" HARD GOLD OVER min. 50µ" NICKEL
4. THREADED INSERT: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
5. PCB-SNAP: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
6. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
7. CONNECTOR IS PART MARKED: DLH5XP8CK53X CONEC Y/WW
8. = CRITICAL DIMENSION

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
4 x b	Ä 2158	09.02.2005	Lehmen

tolerance		
2003	date	name
drawn	12.02.	Parei
appd.	12.02.	Kühle
norm		
d-old		

scale: 2:1
material: SEE NOTES
title: D-SUB HD MALE 90° 78pos. SOLDER PIN ANGLED 0.350inch with threaded insert and clip
dwg no: AutoCAD 2000
16K1A882
part no: DLH5XP8CK53X