


5-2274319-1 Product Details

 [Share](#)  [Print](#)  [Email](#)



 **Active**

Impact High Density Backplane Connectors

IMP100,S,H,V3P8C,LG,OEW46,SL

5-2274319-1 

TE Internal Number: 5-2274319-1

Product Highlights [View All](#)

- Connector Style = Header
- 48/Signal, 24/Ground
- 72 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

[Pricing & Availability](#) 

[Request Sample](#) 

[Add to My Part List](#) 

[Buy Product through
Distributor](#) 

 Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
PCB Mount Retention Type	Action/Compliant Tail
PCB Mount Alignment Type	Locating Post(s)

Electrical Characteristics	
Impedance (Ω)	100
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	120 
Operating Voltage (VDC)	120

Dimensions	
Tail Length (mm [in])	1.2 [0.047]
Length (X-Axis) (mm [in])	21.70 [0.854]
Width (Z-Axis) (mm [in])	16.70 [0.657]
Profile Height (Y-Axis) (mm [in])	11.95 [0.470]
PCB Hole Diameter (mm [in])	0.39 [0.015]

Body Features	
Header Type	Partially Shrouded

Contact Features	
Contact Type	Pin
Contact Length (mm [in])	4.90 [0.193]
Contact Plating, Termination Area, Material	Matte Tin
Contact Plating, Termination Area, Thickness (µm [µin])	1.27 [50]
Contact Base Material	Copper-Nickel-Silicon
Underplate Material	Nickel
Underplate Material Thickness (µm [µin])	1.27 [50.000]

Housing Features	
Connector Style	Header
End Wall Location	Open
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)

Configuration Features	
Connector Contact Configuration (No. of Pos./Type)	48/Signal, 24/Ground
Number of Positions 	72
Number of Differential Pairs Per Column	3
Number of Columns	8
Number of Rows 	9
Shrouded	Yes - Partial
Guide Location	Left 
Tail Orientation	In-line

Industry Standards	
RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0
CSA Certified	Yes

Environmental	
Operating Temperature (°C [°F])	-55 - +85 [-67 - +185]

Conditions for Usage	
Board-to-Board Configuration	Right Angle, Vertical

Operation/Application	
Industry Application	Networking (Communications)

Packaging Features	
Packaging Method	Tube/Box

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)