

## USB 3.0 SuperSpeed A to A M/M Cable, Industrial - IP68, Shielded, 3 ft. (0.91 m), TAA

MODEL NUMBER: U325-003-IND



Connects high-speed USB 3.0 equipment in industrial environments that require protection against dust and moisture.

### Features

**Shielded USB 3.0 Cable Recommended for Outdoor or Harsh Indoor Environments** This three-foot (one-meter) industrial-grade USB-A to USB-A cable is ideal for connecting high-speed USB 3.0 equipment—for instance, a computer or server to a patch bay or industrial hub—in outdoor applications and other areas where protection from harsh elements is essential. The shielded cable and USB-A connectors are designed to withstand dust, debris and moisture that could threaten your IT infrastructure. Included dust caps protect the connectors when not in use.

**IP68 Rating Denotes Resistance to Dust and Water** The IP68 rating means the USB Type-A to USB Type-A cable is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance, making the cable ideal for basement applications. For applications that require IP68 protection, use the industrial cable with a Tripp Lite N206-SB01-IND surface-mount box and U325-000-IND bulkhead coupler. If only IP44 protection against splashing water from all directions is required, pair the cable with a N206-FP01-IND, N206-FP02-IND or N206-FP04-IND metal wall plate and the U325-000-IND coupler.

**Heavy Shielding Protects Your Network Data from Destructive Line Noise** The USB-A to USB-A cable's shielded construction helps fight against EMI/RFI line noise that interferes with your signal and can distort or destroy data. Electromagnetic interference and radio frequency interference can be created by electric motors, power cables, welding equipment and other heavy machinery frequently found in industrial applications.

**Supports USB 3.0 Speeds for a Faster, More Efficient Signal** This USB-A male to USB-A male cable supports USB 3.0 data transfer rates up to 5 Gbps—10 times faster than USB 2.0. Its bi-directional data interface allows data to flow both directions simultaneously, increasing theoretical bandwidth by 10 times for efficient power and little wait-time. The U325-003-IND is also backward compatible with previous USB generations.

**TAA-Compliant for GSA Schedule Purchases** The U325-003-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

**Lifetime Warranty** The U325-003-IND is backed by a lifetime warranty, ensuring reliability and

### Highlights

- Built to protect process control and other USB 3.0 applications in harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Complies with Federal Trade Agreements Act standards for GSA Schedule purchases

### Applications

- Provide USB 3.0 connectivity in outdoor environments susceptible to rain, such as malls, bus stops and theater marquees
- Set up outdoor digital signage at stadiums and arenas
- Build IT infrastructure in basements and other indoor areas prone to flooding

### Package Includes

- U325-003-IND USB-A Male to USB-A Male Cable, SuperSpeed, 3.0/3.1, Industrial, 3 ft. (1 m)

performance.

## Specifications

| OVERVIEW                        |                               |
|---------------------------------|-------------------------------|
| UPC Code                        | 037332209504                  |
| USB Cable Type                  | Passive                       |
| PHYSICAL                        |                               |
| Material of Construction        | PVC                           |
| Cable Jacket Color              | Black                         |
| Cable Outer Diameter (OD)       | 5.5                           |
| Cable Length (ft.)              | 3                             |
| Cable Length (m)                | 0.91                          |
| Cable Length (in.)              | 36                            |
| Cable Length (cm)               | 91                            |
| Shipping Dimensions (hwd / in.) | 9.70 x 6.90 x 0.50            |
| Shipping Dimensions (hwd / cm)  | 24.64 x 17.53 x 1.27          |
| Shipping Weight (lbs.)          | 0.21                          |
| Shipping Weight (kg)            | 0.10                          |
| ENVIRONMENTAL                   |                               |
| Operating Temperature Range     | -4 to 176 F (-20 to 80 C)     |
| Storage Temperature Range       | -4 to 176 F (-20 to 80 C)     |
| Relative Humidity               | 10% to 90% RH, Non-Condensing |
| Operating Humidity Range        | 0% to 90% RH, Non-Condensing  |
| Storage Humidity Range          | 0% to 90% RH, Non-Condensing  |
| CONNECTIONS                     |                               |
| Side A - Connector 1            | USB 3.0 A (MALE)              |
| Side B - Connector 1            | USB 3.0 A (MALE)              |
| Connector Plating               | Nickel                        |
| Contact Plating                 | Gold                          |
| FEATURES & SPECIFICATIONS       |                               |
| USB Specification               | USB 3.0 (up to 5 Gbps)        |
| IP68 Rated                      | Yes                           |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

| STANDARDS & COMPLIANCE              |                                         |
|-------------------------------------|-----------------------------------------|
| Protection Rating                   | IP68                                    |
| Product Certifications              | UL Listed                               |
| Product Compliance                  | RoHS; REACH; Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT                  |                                         |
| Product Warranty Period (Worldwide) | Lifetime limited warranty               |



© 2022 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.