






REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	B	REVISED PER ECR-16-005516	25APR2016	DD	CS



ISOMETRIC VIEW
SCALE 10:1





SECTION AF-AF
SCALE 20:1



SECTION N-N
SCALE 20:1

- 1 MATERIAL: 0.2mm THICK CuNiSi ALLOY
- 2 FINISH: PRE-PLATED WITH 1.00µm MIN BRIGHT TIN
- 3 MATERIAL ID FEATURE IN "DOWN" POSITION
4. THIS PRODUCT DESIGNED TO COMPLY WITH USCAR-2, REVISION 5 TEMP CLASS 3, MOUNTED TO ENGINE VIBRATION PROFILE
5. THIS PRODUCT IS DESIGNED TO BE COMPATIBLE WITH SEALED APPLICATIONS.
6. NORMAL FORCE 240 GRAMS REFERENCE.
7. TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT AND VISIBILITY MAY VARY.
- 8 NOT INTENDED FOR SEALED APPLICATIONS.
- 9 SEALING CAPABILITY MUST BE EVALUATED ON AN APPLICATION BASIS.



1.10-1.40	2.38	1.40	2.40	1.70	0.80	1.85	FIGURE 2	0.35	22	2098762-8	9				
0.85-1.05	2.09	0.85	1.82	1.46	0.65	1.50	FIGURE 2	0.13	26	2098762-7	8				
2.06 MAX	3.09	1.78	2.94	2.43	1.00	1.96	FIGURE 2	0.75	18	2098762-6					
1.50-1.85	3.09	1.78	2.94	2.23	0.80	1.82	FIGURE 2	0.35-0.50	20-22	2098762-5					
1.10-1.40	2.38	1.40	2.40	1.70	0.80	1.85	FIGURE 1	0.35	22	2098762-4	9				
0.85-1.05	2.09	0.85	1.82	1.46	0.65	1.50	FIGURE 1	0.13	26	2098762-3	8				
2.06 MAX	3.09	1.78	2.94	2.43	1.00	1.96	FIGURE 1	0.75	18	2098762-2					
1.50-1.85	3.09	1.78	2.94	2.23	0.80	1.82	FIGURE 1	0.35-0.50	20-22	2098762-1					
INSULATION DIAMETER	T	S	R	L	K	J	REELING DIRECTION	mm ²	AWG	PART NUMBER					
	DIMENSION							WIRE SIZE							
THIS DRAWING IS A CONTROLLED DOCUMENT.							DWN 04FEB2010		 TE Connectivity						
DIMENSIONS:							CHK 04FEB2010								
mm							APVD 04FEB2010		NAME						
							PRODUCT SPEC								
							-								
							APPLICATION SPEC								
							114-13183								
MATERIAL							SIZE		CAGE CODE			DRAWING NO	RESTRICTED TO		
-							A1		00779			C=2098762	-		
-							CUSTOMER DRAWING		SCALE			15:1	SHEET 1 OF 1	REV B	