

# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, shielded: yes, degree of protection: IP67, cable diameter range: 2 mm ... 14.5 mm, number of positions: 26, connection method: Solder connection, series: HC, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240137

## Commercial data

Item number	1590285
Packing unit	12 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAJA
GTIN	4046356186582
Weight per piece (including packing)	99.63 g
Weight per piece (excluding packing)	87.839 g
Customs tariff number	85366990
Country of origin	DE

# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	FPM

### Connection data

#### Conductor connection

Connection method	Solder connection
-------------------	-------------------

### Electrical properties

#### Contact

Contact diameter	1 mm
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
Max. current	8 A
Nominal voltage U <sub>N</sub>	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

### Connector

Type	straight
------	----------

# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

Direction of rotation	Standard
-----------------------	----------

## Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M27

## Cable/line

External cable diameter	2 mm ... 14.5 mm
-------------------------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (When plugged in)
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# HC-26P1N1280DU - Cable connector


1590285

<https://www.phoenixcontact.com/us/products/1590285>



## Drawings

Dimensional drawing



Dimensional drawing


# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

Schematic diagram



Connector pin assignment

# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

## Classifications

### ECLASS

ECLASS-13.0	27440116
-------------	----------

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-26P1N1280DU - Cable connector



1590285

<https://www.phoenixcontact.com/us/products/1590285>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c70cfe42-4676-41fd-9436-9f6c2b4f79c8

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)