



5

4



3

2

1



Printed board layout
component side



Connector retention and insertion forces on the PCB = 25 / 80 Newtons.

09 65 361 6733	M3	2					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 25 poles, male, straight with solder pins 3,7 screw lock and grounding board lock.	Maßstab/ Scale 1.5:1
09 65 361 7733	M3	3				Detail.	07-FEB-02	JB			
09 65 361 5733	M3	0,76 µm Au				Insp.					
09 65 361 6713	4-40 UNC	2				Stand.					
09 65 361 7713	4-40 UNC	3	29723	05-MAR-02	CV	HARTING EURL F-95972 Paris				TB 09 65 361 x7x3	Blatt/ Page 1
09 65 361 5713	4-40 UNC	0,76 µm Au	29746	07-FEB-02	JB						
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name						

09 65 361 5713
Printed board connector

Other applications

gender	male connector, straight
Termination	Stamped solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Board fixing	with grounding board lock
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



The data sheet is up to date
2D files

Typenblatt

Typenblatt