

**SURFACE MOUNT
GLASS PASSIVATED RECTIFIERS**

**REVERSE VOLTAGE -50 to 1000 Volts
FORWARD CURRENT – 1.5 Amperes**


FEATURES

- Glass passivated chip
- For surface mounted applications
- Low reverse leakage current
- Low forward voltage drop
- High current capability

MECHANICAL DATA

- Case: Molded plastic
- Case Material molding compound, UL flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free".
- Polarity: Color band denotes cathode
- Weight : 0.003 ounces, 0.093 grams

SMB



SMB		
DIM.	MIN.	MAX.
A	4.06	4.57
B	3.30	3.94
C	1.96	2.21
D	0.15	0.31
E	5.21	5.59
F	0.05	0.20
G	2.01	2.50
H	0.76	1.52

All dimension in millimeter

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	S2A	S2B	S2D	S2G	S2J	S2K	S2M	UNIT
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current @ $T_L=100^\circ\text{C}$	$I_{(AV)}$				1.5				A
Peak forward surge current single half sine-wave superimposed on rated load. (JDEEC METHOD)	I_{FSM}	@ 8.3ms @ 1ms			50 100				A
I^2t rating for fusing (1ms $\leq t \leq 8.3\text{ms}$)	I^2t				10.4				A^2S
Typical junction capacitance (Note1)	C_J				20				pF
Operation and storage temperature range	T_J, T_{STG}				-55 to +150				$^\circ\text{C}$

STATIC ELECTRICAL CHARACTERISTICS

PARAMETER	TEST CONDITIONS	SYMBOL	MAX.	UNIT
Forward voltage	$IF=1.5\text{A}$	V_F	1.15	V
Leakage current	VR rated	I_R	5.0 125	μA

THERMAL CHARACTERISTICS

PARAMETER	SYMBOL	TYP.	UNIT
Typical thermal resistance (Note2)	R_{thJ_L}	20	$^\circ\text{C/W}$

DYNAMIC ELECTRICAL CHARACTERISTICS

PARAMETER	TEST CONDITIONS	SYMBOL	TYP.	UNIT
Reverse recovery time	$IF= 0.5\text{A}$, $Ir= 0.25\text{A}$, $IR = 1.0\text{A}$	T_{RR}	1500	ns

Note :

- (1) Measured at 1.0MHz and applied reverse voltage of 4.0V DC.
- (2) Thermal resistance junction to lead.

REV. 8, DEC.-2014, KSDB02

Please be aware that an **Important Notice and Disclaimer** concerning availability, disclaimers, and use in critical applications of LSC products thereto appears at the end of this Data Sheet.

RATING AND CHARACTERISTIC CURVES
S2A thru S2M

LITEON

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3- TYPICAL FORWARD CHARACTERISTICS





FIG.4- TYPICAL REVERSE CHARACTERISTICS



IMPORTANT NOTICE AND DISCLAIMER

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design purchase or use.

All information are provided as-is, even it has qualified by the AEC-Q101 which satisfy industrial application requirement, except as expressly stated in this data sheet is applied for automotive grade, LSC make no warranties, representation or guarantee, whether express, implied or statutory, including, without limitation, regarding any merchantability, satisfactory quality, or fitness for a particular purpose with respect to the LSC technology.

LSC does not assume any liability or compensation for any application assistance or customer product design, and make no warranty or accept any liability with products, which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.