




MQS

TE Internal #: 1-1355135-1

Violet, TPA (Terminal Position Assurance), PA GF, -40 – 120 °C [-40 – 248 °F]

[View on TE.com >](#)

Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Primary Product Color: **Violet**

Connector & Contact Retention Accessory Type: **TPA (Terminal Position Assurance)**

Primary Product Material: **PA GF**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Sealable	No
Connector & Contact Retention Accessory Type	TPA (Terminal Position Assurance)

Body Features

Primary Product Color	Violet
Primary Product Material	PA GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Serviceable	Yes
-------------	-----

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought






TE Part #K1162562
Relay 29-111-12-A-961




TE Part #K2001883
Toggle Switch 08-2-2-13 F



TE Part #K1162563
Relay 29-011-12-A-960



TE Part #184060-1
6 POS./6 CIRC PLUG ASSY, KEY A



TE Part #1393364-2
V23540X7000Y 12=GET FEM TERM A



TE Part #1473288-1
MICRO TIMER II 6POS SECONDARY



TE Part #1-1718484-3
CARRIER FOR RECEPTACLE INSERTS



TE Part #2005372-2
MT-II SLD 6P PLUG ASSY(A) BLK



TE Part #2005390-6
JPT SLD 3P PLUG ASSY-1S BLK



TE Part #284722-1
COVER FOR 94 POS. RECEPTACLE HOUSING

Documents

Product Drawings

RETAINER 94P

English

RETAINER 94P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1355135-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1355135-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1355135-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Product Specification

English

Modular Jack, Single or Dual Port, Surface Mount or Thru-Hole, Economy

English