




Part Number : [5039600696](#)

Product Description : 1.42mm Height micro-SIM Card Connector, 1.00mm Pitch, Push-Push, Surface Mount, Normal Mount, with Detect Switch, Stainless Steel Shell, 6 Circuits

Series Number : 503960

Status : Active

Product Category : Memory / SIM Card Connectors



Documents and Resources

Drawings

[5039600696 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)


Specifications

[SPK-503960-001-001.pdf](#)

[PS-503960-006-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Memory / SIM Card Connectors
Series	503960
Description	1.42mm Height micro-SIM Card Connector, 1.00mm Pitch, Push-Push, Surface Mount, Normal Mount, with Detect Switch, Stainless Steel Shell, 6 Circuits
Product Name	micro-SIM
Style	Push-Push
UPC	889056143127

Electrical

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	10V AC (RMS)/DC

Physical

Card Detection Switch	Closed
Card Entry Location	Front
Circuits (Loaded)	6

Color - Resin	Black
Durability (mating cycles max)	2000
Ejector Button Side	N/A
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Material - Shell	Stainless Steel
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.54mm
Temperature Range - Operating	-25° to +85°C
Termination Interface Style	Surface Mount

This document was generated on May 04, 2026