

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECO-19-012048	04AUG2019	MY	DZ
-	-		-	-	-
-	-		-	-	-
-	-		-	-	-

D

D

C


C

B

B


A

A



1. ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTICTED SUBSTANCES).
2. NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702.
3. ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, AND SIGNAL INTEGRITY.
4. CABLE BEND RADIUS 5X BUNDLE CABLE OD.
5. SEE SHEETS 2 AND 3 FOR WIRING SCHEMATIC.
6. CONNECTORS ARE GEN-Z COMPATIBLE.

△ LABEL INFORMATION SHOWN BELOW:



8. CABLE CONNECTOR MATES WITH TE SLIVER RECEPTACLE P/N 2331813-X, OR 2331814-X.

500	1000 +10/-0	2343286-2
250	500 +10/-0	2343286-1
("M")	"L"	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SMITH 10DEC2018	TE TE Connectivity	
DIMENSIONS:		CHK GLEN GUTGOLD 10DEC2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD GLEN GUTGOLD 10DEC2018	NAME SLIVER 2.0 2C 33 AWG LATERAL TO LATERAL	
		PRODUCT SPEC		
	0 PLC ±	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
		WEIGHT		
MATERIAL SEE BOM	FINISH	RESTRICTED CUSTOMER	A100779C=2343286	
			SCALE 3:2	SHEET 1 OF 2 REV A

