



**Part Number :** [09652058](#)


**Product Description :** SPOX and KK 396 Wire-to-Board Header, Vertical, with Friction Lock, 5 Circuits

**Series Number :** 5273

**Status :** Active

**Product Category :** PCB Headers and Receptacles

**Engineering Part Number :** 5273-05A



---

## Documents and Resources

### Drawings

[009652058\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-09-65-2058-001.zip](#)

### Specifications

[SPK-5273-001-001.pdf](#)

[PS-5195-001-001.pdf](#)

[PS-5195-005-001.pdf](#)

[PS-5239-002-001.pdf](#)

[PS-5239-004-001.pdf](#)

[PS-5239-006-001.pdf](#)

[PS-5239-007-001.pdf](#)

[PS-5273-003-001.pdf](#)

[PS-5273-004-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	5273
Description	SPOX and KK 396 Wire-to-Board Header, Vertical, with Friction Lock, 5 Circuits
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK 396,SPOX
UPC	800753613683

### Agency

CSA	LR19980
-----	---------

UL	E29179
----	--------

## Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

## Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1709.100/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.60mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No

Shrouded	Partially Shrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
SPOX 3.96mm Pitch Single Row Receptacle Housings	<u>5195</u>

---

This document was generated on May 06, 2026