

HC-EVO-B10-HLWD-EL-AL - Housing



1411457

<https://www.phoenixcontact.com/us/products/1411457>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON EVO sleeve housing, EMC version, without powder coating, with bayonet flange for EVO screw connection, B10, with double locking latch, height: 64 mm, without EVO screw connection.

Your advantages

- Flexible cable outlet direction, lateral or straight

Commercial data

Item number	1411457
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	BF7APM
Catalog page	Page 613 (C-2-2019)
GTIN	4046356932646
Weight per piece (including packing)	166 g
Weight per piece (excluding packing)	141.733 g
Customs tariff number	85389099
Country of origin	DE

HC-EVO-B10-HLWD-EL-AL - Housing



1411457

<https://www.phoenixcontact.com/us/products/1411457>

Technical data


Notes

General	For contact inserts HC-B10, BB18, DD42, M, K8/24
---------	--

Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B10
No. of cable outlets	1
Type	Low design
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	44 mm
Height	64 mm
Length	73 mm

Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Locking latch material	PA

Mechanical properties

Mechanical data	
Locking type	Latch

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

HC-EVO-B10-HLWD-EL-AL - Housing


1411457

<https://www.phoenixcontact.com/us/products/1411457>



Drawings

Dimensional drawing



Dimensional drawing

HC-EVO-B10-HLWD-EL-AL - Housing



1411457

<https://www.phoenixcontact.com/us/products/1411457>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411457>



DNV
Approval ID: TAE000037S



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026



EAC
Approval ID: RU C-DE.AI30.B.01102



EAC
Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

HC-EVO-B10-HLWD-EL-AL - Housing



1411457

<https://www.phoenixcontact.com/us/products/1411457>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-EVO-B10-HLWD-EL-AL - Housing



1411457

<https://www.phoenixcontact.com/us/products/1411457>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



Accessories

HC-B-G-M20-EC-AL - Cable gland

1411439

<https://www.phoenixcontact.com/us/products/1411439>



EVO EMC cable gland with bayonet locking, B series, size M20, cable diameter:
9 ... 13 mm

HC-B-G-M25-EC-AL - Cable gland

1411446

<https://www.phoenixcontact.com/us/products/1411446>



EVO EMC cable gland with bayonet locking, B series, size M25, cable diameter:
11 ... 16 mm

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



HC-B-G-M32-EC-AL - Cable gland

1411440

<https://www.phoenixcontact.com/us/products/1411440>



EVO EMC cable gland with bayonet locking, B series, size M32, cable diameter:
14 ... 21 mm

HC-B-G-M20-ER-AL - Cable gland

1411442

<https://www.phoenixcontact.com/us/products/1411442>



EVO metal cable gland with bayonet locking, B series, size M20, cable diameter:
7 - 13 mm

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



US-EMLP-HA (20X9) - Plastic label

0830989

<https://www.phoenixcontact.com/us/products/0830989>



Plastic label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 20 x 9 mm, Number of individual labels: 70

HC-B-G-M25-ER-AL - Cable gland

1411443

<https://www.phoenixcontact.com/us/products/1411443>



EVO metal cable gland with bayonet locking, B series, size M25, cable diameter: 11 - 16 mm

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



HC-B-G-M32-ER-AL - Cable gland

1411444

<https://www.phoenixcontact.com/us/products/1411444>



EVO metal cable gland with bayonet locking, B series, size M32, cable diameter:
14 - 21 mm

HC-B-G-M40-ER-AL - Cable gland

1411445

<https://www.phoenixcontact.com/us/products/1411445>



EVO metal cable gland with bayonet locking, B series, size M40, cable diameter:
19 - 27 mm

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



HC-B-G-M40-EC-AL - Cable gland

1411441

<https://www.phoenixcontact.com/us/products/1411441>



EVO EMC cable gland with bayonet locking, B series, size M40, cable diameter:
19 ... 27 mm

HC-B10-HCFD-PR-BK - Protective cover

1346529

<https://www.phoenixcontact.com/us/products/1346529>



Protective cover B10, for double locking latch, protective cover material: PC,
height: 26.3 mm, seal: yes

HC-EVO-B10-HLWD-EL-AL - Housing

1411457

<https://www.phoenixcontact.com/us/products/1411457>



US-EMLP-HA (20X9) CUS - Plastic label

0830995

<https://www.phoenixcontact.com/us/products/0830995>

Plastic label, Card, white, labeled, can be labeled with: THERMOMARK CARD, mounting type: adhesive, lettering field size: 20 x 9 mm, Number of individual labels: 70



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com