


 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- 10/100BASE-T Ethernet Application
- Component Type = Stacked
- Magnetic Circuit = S866P9
- Turns Ratio = 1:1
- 2 x 1 Jack Configuration

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- None Available

- None Available

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

- Signal Routing Type = Auto MDI/MDIX, HUB
- PCB Mount Style = Thru Hole
- Shielded = Yes
- Shield Material = Brass

- Jack Configuration = 2 x 1

- Component Type = Stacked
- Turns Ratio = 1:1
- Impedance (Ω) = 100

- Bottom Panel Ground Tab = With

- LED = With
- Shield Panel Ground Tabs = With
- Bottom Shield = Without
- Shield Plating = Semi-Bright Nickel (Pre-plated)
- PCB Tail Length (mm [in]) = 3.04 [0.119]

- Housing Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic Polyester (PBT)

- Magnetic Circuit = S866P9
- Upper Left LED Color (Top LED Position #2) = Green
- Upper Right LED Color (Top LED Position #1) = Yellow
- Decoupling Capacitor = 2KV
- Rear PCB Ground Tab = Without
- Signal Lead Quantity = 6

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Lower Left LED Color (Bottom LED Position #2)
= Green
- Lower Right LED Color (Bottom LED Position #1) = Yellow

- Temperature Rating = Office / Premises (0 °C to +70 °C)

- Application = 10/100BASE-T Ethernet

- Insulator = Without
- Brand = Tyco Electronics