



**Part Number :** [1461530200](#)

**Product Description :** Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

**Series Number :** 146153

**Status :** Active

**Product Category :** Antennas



---

## Documents and Resources

### Drawings

[1461530200\\_sd.pdf](#)

[1461530100-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[AS-146153-100-001.pdf](#)

[PS-146153-100-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Antennas
Series	146153
Description	Wi-Fi 6E Flex Cabled Balanced Antenna, 9.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	2.4/5GHz Balanced Flex Antenna
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Internal, Wi-Fi Antenna
UPC	889056310833

### Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5930
Band#2 F_Start (MHz)	4900
Electrical Connectivity	Cable

Peak Gain (dBi)	2.6 @ 2.4 GHz, 3.5 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>66% @ 5 GHz, >69% @ 2.4 GHz

## Physical

Cable Length	200.00mm
Length	34.90mm
Mounting Style	Adhesive
Net Weight	0.920/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	9.00mm

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

---

This document was generated on May 21, 2026