

**MOSFET – N-Channel,  
SUPERFET® II****600 V, 7.4 A, 600 mΩ****FCP600N60Z,  
FCPF600N60Z****Description**

SUPERFET II MOSFET is onsemi's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This technology is tailored to minimize conduction loss, provide superior switching performance, dv/dt rate and higher avalanche energy. Consequently, SUPERFET II MOSFET is very suitable for the switching power applications such as PFC, server/telecom power, FPD TV power, ATX power and industrial power applications.

**Features**





- 650 V @  $T_J = 150^\circ\text{C}$
- Typ.  $R_{DS(on)} = 510 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ.  $Q_g = 20 \text{ nC}$ )
- Low Effective Output Capacitance (Typ.  $C_{oss(\text{eff.})} = 74 \text{ pF}$ )
- 100% Avalanche Tested
- ESD Improved Capacity
- RoHS Compliant

**Applications**

- LCD/LED/PDP TV and Monitor Lighting
- Solar Inverter
- AC-DC Power Supply

$V_{DSS}$	$R_{DS(\text{ON}) \text{ MAX}}$	$I_D \text{ MAX}$
600 V	0.6 $\Omega$ @ 10 V	7.4 A*

\*Drain current limited by maximum junction temperature.

TO-220-3LD  
CASE 340ATTO-220 Fullpack, 3-Lead  
/ TO-220F-3SG  
CASE 221AT**MARKING DIAGRAM**

FCP(F)600N60Z = Device Code  
A = Assembly Location  
YWW = Date Code (Year & Week)  
ZZ = Assembly Lot

**ORDERING INFORMATION**

Device	Package	Shipping
FCP600N60Z	TO-220-3LD	800 Units / Tube
FCPF600N60Z	TO-220 Fullpack	1000 Units / Tube

# FCP600N60Z, FCPF600N60Z

MOSFET MAXIMUM RATINGS ( $T_C = 25^\circ\text{C}$  unless otherwise noted)

Symbol	Parameter		FCP600N60Z	FCPF600N60Z	Unit
$V_{DSS}$	Drain to Source Voltage		600		V
$V_{GSS}$	Gate to Source Voltage	-DC	$\pm 20$		V
		-AC ( $f > 1 \text{ Hz}$ )	$\pm 30$		
$I_D$	Drain Current	- Continuous ( $T_C = 25^\circ\text{C}$ )	7.4	7.4*	A
		- Continuous ( $T_C = 100^\circ\text{C}$ )	4.7	4.7*	
$I_{DM}$	Drain Current	- Pulsed (Note 1)	22.2	22.2*	A
$E_{AS}$	Single Pulsed Avalanche Energy (Note 2)		135		mJ
$I_{AR}$	Avalanche Current (Note 1)		1.5		A
$E_{AR}$	Repetitive Avalanche Energy (Note 1)		0.89		mJ
$dv/dt$	MOSFET $dv/dt$		100		V/ns
	Peak Diode Recovery $dv/dt$ (Note 3)		20		
$P_D$	Power Dissipation	( $T_C = 25^\circ\text{C}$ )	89	28	W
		-Derate above $25^\circ\text{C}$	0.71	0.22	$\text{W}/^\circ\text{C}$
$T_J, T_{STG}$	Operating and Storage Temperature Range		-55 to +150		$^\circ\text{C}$
$T_L$	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 Seconds		300		$^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

\*Drain current limited by maximum junction temperature.

1. Repetitive rating: pulse-width limited by maximum junction temperature.

2.  $I_{AS} = 1.5 \text{ A}$ ,  $V_{DD} = 50 \text{ V}$ ,  $R_G = 25 \Omega$ , starting  $T_J = 25^\circ\text{C}$ .

3.  $I_{SD} \leq 3.7 \text{ A}$ ,  $di/dt \leq 200 \text{ A/us}$ ,  $V_{DD} \leq BV_{DSS}$ , starting  $T_J = 25^\circ\text{C}$ .

## THERMAL CHARACTERISTICS

Symbol	Parameter	FCP600N60Z	FCPF600N60Z	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max.	1.4	4.5	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	62.5	62.5	

# FCP600N60Z, FCPF600N60Z

ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$  unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>						
$\text{BV}_{\text{DSS}}$	Drain to Source Breakdown Voltage	$V_{\text{GS}} = 0 \text{ V}$ , $I_D = 10 \text{ mA}$ , $T_J = 25^\circ\text{C}$	600	–	–	V
		$V_{\text{GS}} = 0 \text{ V}$ , $I_D = 10 \text{ mA}$ , $T_J = 150^\circ\text{C}$	650	–	–	
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = 10 \text{ mA}$ , referenced to $25^\circ\text{C}$	–	0.67	–	$\text{V}/^\circ\text{C}$
$\text{BV}_{\text{DS}}$	Drain to Source Avalanche Breakdown Voltage	$V_{\text{GS}} = 0 \text{ V}$ , $I_D = 7.4 \text{ A}$	–	700	–	V
$I_{\text{DSS}}$	Zero Gate Voltage Drain Current	$V_{\text{DS}} = 600 \text{ V}$ , $V_{\text{GS}} = 0 \text{ V}$	–	–	1	$\mu\text{A}$
		$V_{\text{DS}} = 480 \text{ V}$ , $T_C = 125^\circ\text{C}$	–	1.32	–	
$I_{\text{GSS}}$	Gate to Body Leakage Current	$V_{\text{GS}} = \pm 20 \text{ V}$ , $V_{\text{DS}} = 0 \text{ V}$	–	–	$\pm 10$	$\mu\text{A}$
<b>ON CHARACTERISTICS</b>						
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{GS}} = V_{\text{DS}}$ , $I_D = 250 \mu\text{A}$	2.5	–	3.5	V
$R_{\text{DS(on)}}$	Static Drain to Source On Resistance	$V_{\text{GS}} = 10 \text{ V}$ , $I_D = 3.7 \text{ A}$	–	0.51	0.6	$\Omega$
$g_{\text{FS}}$	Forward Transconductance	$V_{\text{DS}} = 20 \text{ V}$ , $I_D = 3.7 \text{ A}$	–	6.7	–	S
<b>DYNAMIC CHARACTERISTICS</b>						
$C_{\text{iss}}$	Input Capacitance	$V_{\text{DS}} = 25 \text{ V}$ , $V_{\text{GS}} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	–	840	1120	pF
$C_{\text{oss}}$	Output Capacitance		–	630	840	pF
$C_{\text{rss}}$	Reverse Transfer Capacitance		–	30	45	pF
$C_{\text{oss}}$	Output Capacitance	$V_{\text{DS}} = 380 \text{ V}$ , $V_{\text{GS}} = 0 \text{ V}$ , $f = 1 \text{ MHz}$	–	16.5	–	pF
$C_{\text{oss(eff.)}}$	Effective Output Capacitance	$V_{\text{DS}} = 0 \text{ V}$ to $480 \text{ V}$ , $V_{\text{GS}} = 0 \text{ V}$	–	74	–	pF
$Q_{\text{g(tot)}}$	Total Gate Charge at 10 V	$V_{\text{DS}} = 380 \text{ V}$ , $I_D = 3.7 \text{ A}$ , $V_{\text{GS}} = 10 \text{ V}$ (Note 4)	–	20	26	nC
$Q_{\text{gs}}$	Gate to Source Gate Charge		–	3.4	–	nC
$Q_{\text{gd}}$	Gate to Drain "Miller" Charge		–	7.5	–	nC
ESR	Equivalent Series Resistance	$f = 1 \text{ MHz}$	–	2.89	–	$\Omega$
<b>SWITCHING CHARACTERISTICS</b>						
$t_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}} = 380 \text{ V}$ , $I_D = 3.7 \text{ A}$ , $V_{\text{GS}} = 10 \text{ V}$ , $R_G = 4.7 \Omega$ (Note 4)	–	13	36	ns
$t_r$	Turn-On Rise Time		–	7	24	ns
$t_{\text{d(off)}}$	Turn-Off Delay Time		–	39	88	ns
$t_f$	Turn-Off Fall Time		–	9	28	ns
<b>DRAIN-SOURCE DIODE CHARACTERISTICS</b>						
$I_{\text{S}}$	Maximum Continuous Drain to Source Diode Forward Current	–	–	7.4	–	A
$I_{\text{SM}}$	Maximum Pulsed Drain to Source Diode Forward Current	–	–	22.2	–	A
$V_{\text{SD}}$	Drain to Source Diode Forward Voltage	$V_{\text{GS}} = 0 \text{ V}$ , $I_{\text{SD}} = 3.7 \text{ A}$	–	–	1.2	V
$t_{\text{rr}}$	Reverse Recovery Time	$V_{\text{GS}} = 0 \text{ V}$ , $I_{\text{SD}} = 3.7 \text{ A}$ , $dI_F/dt = 100 \text{ A}/\mu\text{s}$	–	200	–	ns
$Q_{\text{rr}}$	Reverse Recovery Charge		–	2.3	–	$\mu\text{C}$

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics










Figure 6. Gate Charge Characteristics

TYPICAL PERFORMANCE CHARACTERISTICS (continued)



## TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 13. Transient Thermal Response Curve for FCP600N60Z




Figure 14. Transient Thermal Response Curve for FCPF600N60Z

## FCP600N60Z, FCPF600N60Z




Figure 15. Gate Charge Test Circuit & Waveform




Figure 16. Resistive Switching Test Circuit & Waveforms




Figure 17. Unclamped Inductive Switching Test Circuit & Waveforms

## FCP600N60Z, FCPF600N60Z









Figure 18. Peak Diode Recovery  $dv/dt$  Test Circuit & Waveforms

SUPERFET is a registered trademark of Semiconductor Components Industries, LLC dba “onsemi” or its affiliates and/or subsidiaries in the United States and/or other countries.



TO-220 Fullpack, 3-Lead / TO-220F-3SG  
CASE 221AT  
ISSUE B

DATE 19 JAN 2021




DIM	MILLIMITERS		
	MIN	NOM	MAX
A	4.50	4.70	4.90
A1	2.56	2.76	2.96
A2	2.34	2.54	2.74
b	0.70	0.80	0.90
b2	~	~	1.47
C	0.45	0.50	0.60
D	15.67	15.87	16.07
D1	15.60	15.80	16.00
E	9.96	10.16	10.36
e	2.34	2.54	2.74
F	~	0.84	~
H1	6.48	6.68	6.88
L	12.78	12.98	13.18
L1	3.03	3.23	3.43
Ø P	2.98	3.18	3.38
Ø P1	~	1.00	~
Q	3.20	3.30	3.40

NOTES:

- A. DIMENSION AND TOLERANCE AS ASME Y14.5-2009
- B. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.
- C. OPTION 1 - WITH SUPPORT PIN HOLE
- OPTION 2 - NO SUPPORT PIN HOLE


DOCUMENT NUMBER:	98AON67439E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-220 FULLPACK, 3-LEAD / TO-220F-3SG	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

TO-220-3LD  
CASE 340AT  
ISSUE B


DATE 08 AUG 2022

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	4.00	--	4.70
A1	SEE NOTE "F"		
A2	2.10	--	2.85
b	0.55	--	1.00
b2	1.10	--	1.62
b4	1.42	--	1.62
c	0.36	--	0.60
D	13.90	--	16.30
D1	8.13	--	9.40
D2	11.50	--	14.30
D3	15.42	--	16.51
E	9.65	--	10.67
E1	7.59	--	8.65
e	2.40	--	2.67
H1	6.06	--	6.69
L	12.70	--	14.04
L1	2.70	--	4.10
P	3.50	--	4.00
Q	2.50	--	3.40
z	2.13 REF		
z1	2.06 REF		
Θ	3°	—	5°

GENERIC  
MARKING DIAGRAM\*

XXXXX
XXXXX
AYWWZZ

XXXX = Specific Device Code  
 A = Assembly Location  
 Y = Year  
 WW = Work Week  
 ZZ = Assembly Lot Code



\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.

NOTES:

- A) REFERENCE JEDEC, TO-220, VARIATION AB
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DIMENSIONS COMMON TO ALL PACKAGE SUPPLIERS EXCEPT WHERE NOTED [ ].
- D) LOCATION OF MOLDED FEATURE MAY VARY (LOWER LEFT CORNER, LOWER CENTER AND CENTER OF THE PACKAGE).
- △ DOES NOT COMPLY JEDEC STANDARD VALUE.
- F) "A1" DIMENSIONS AS BELOW:
  - SINGLE GAUGE = 0.51 - 0.61
  - DUAL GAUGE = 1.10 - 1.45
- △ PRESENCE IS SUPPLIER DEPENDENT
- H) SUPPLIER DEPENDENT MOLD LOCKING HOLES IN HEATSINK.

DOCUMENT NUMBER:	98AON13818G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-220-3LD	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

