


28L0138-40R-10

PHYSICAL DIMENSIONS:

A	3.51 [.138]	+ 0.25 [.010]
B	59.00 [2.32]	+ 1.57 [.062]
C	8.89 [.350]	+ 0.51 [.020]
D	0.64 [.025]	+ 0.05 [.002]




ELECTRICAL CHARACTERISTICS:

	Z (Ω) @		DCR (Ω)	Rated Current
	25 MHz	100MHz		
Nominal	99	135		
Minimum	—	101		
Maximum	—	169	0.01	5,000 mA

RoHS

|Z| , R, AND X vs. FREQUENCY



NOTES: UNLESS OTHERWISE SPECIFIED


1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 14" REELS, 4500 PCS/REEL.
2. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
3. WIRE: C10200 OXYGEN FREE COPPER (99.95 MIN.) 22AWG (.025 DIA.)
4. PLATING: 100% TIN $5\mu \pm 2\mu$ [200 $\mu\text{in} \pm 80\mu\text{in}$]
5. WEIGHT/1000: .411 kgs. .905 lbs.
6. REFERENCE STEWARD CORE P/N 28B0138-*00.

DIMENSIONS ARE IN mm (INCHES).				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.		
H	ADD ROHS SYMB. UPDATE COMPANY LOGO	04/20/07	JRK			
G	CHANGE P/N (ADD -10) CHG NOTE 3 ADD NO LEAD SYMBOL, CORRECT WGT.	10/14/03	JRK	PROJECT/PART NUMBER: 28L0138-40R-10		
F	UPDATE FORMAT, CHG RATED CURRENT FROM 10,000 ADDED NOTES	10/11/01	JRK			
E	ADDED (*NOTE&DIM) ON SHT30F4 CORRECTED DIM D ON SHEET 20F4	10/13/98	DTR	REV	PART TYPE:	DRAWN BY:
D	SEE PAGE 30F4 FOR CHGS	07/15/98	DTR	H	ASSEMBLY	DTR
C	UPDATE PRINT FORMAT	06/25/98	DTR	SCALE:	NTS	SHEET:
REV	DESCRIPTION	DATE	INT	TOOL #	B0138	1 of 2


AGILENT E4991A RF Impedance/Material Analyzer
HP 16194A Test Fixture

RoHS

28L0138-40R-10




A	52.4 [2.06]	± 1.50 [.059]
B	1.19 [.047]	MAX.
C	5.00 [.197]	± 0.51 [.020]
D	3.18 [.125]	TYP.
E	0.81 [.032]	MAX.
F	6.35 [.250]	± 0.41 [.016]
G	65.1 [2.56]	TYP.
* Z1	21.72 [.855]	TYP.
Z2	21.72 [.855]	TYP.



A	355.6 ± 2.0 [14.00 $\pm .078$]
B	77.47 ± 1.0 [3.05 $\pm .039$]
C	15.88 ± 0.5 [.625 $\pm .020$]
W	71.1 ± 1.0 [2.80 $\pm .039$]
T	2.16 [.085]

UNIT MEASUREMENT:
mm / inches



* REF. EIA 296 E "LEAD TAPING OF COMPONENTS IN AXIAL LEAD CONFIGURATION FOR AUTOMATIC HANDLING".

NO MORE THAN 1.40 [.055] DIFFERENCE BETWEEN Z1 & Z2

DIMENSIONS ARE IN mm (INCHES).				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
H	ADD ROHS SYMB. UPDATE COMPANY LOGO	04/20/07	JRK	Laird 28L0138-40R-10			
G	CHANGE P/N (ADD -10) CHG NOTE 3 ADD NO LEAD SYMBOL, CORRECT WEIGHT	10/14/03	JRK				
F	UPDATE FORMAT, CHG RATED CURRENT FROM 10,000 ADDED NOTES	10/11/01	JRK				
E	ADDED (*NOTE&DIM) ON SHT30F4 CORRECTED DIM D ON SHEET 20F4	10/13/98	DTR				
D	CHANGE DIM. "G" ON THE TAPE & MODIFIED THE DIMENSIONS ON THE REEL	07/15/98	DTR				
C	UPDATE PRINT FORMAT	06/25/98	DTR	DATE:	06/30/98	SCALE:	NTS
REV	DESCRIPTION	DATE	INT	CAD #	28L0138-40R-10-H-3	TOOL #	B0138
				PROJECT/PART NUMBER:	28L0138-40R-10	REV	H
				PART TYPE:	ASSEMBLY	DRAWN BY:	DTR
				SHEET:	2 of 2		