



TABLE 1	
AHSP P/N	LENGTH "A" (mm)
FOQQA33P00001	1000 ⁺ 50MM
FOQQA33P00002	2000 ⁺ 100MM
FOQQA33P00003	3000 ⁺ 150MM
FOQQA33P00004	4000 ⁺ 150MM
FOQQA33P00005	5000 ⁺ 150MM
FOQQA33P00006	6000 ⁺ 200MM
FOQQA33P00007	7000 ⁺ 200MM
FOQQA33P00008	8000 ⁺ 200MM
FOQQA33P00009	9000 ⁺ 200MM
FOQQA33P00010	10000 ⁺ 300MM
FOQQA33P00012	12000 ⁺ 300MM
FOQQA33P00015	15000 ⁺ 300MM
FOQQA33P00020	20000 ⁺ 500MM
FOQQA33P00025	25000 ⁺ 500MM
FOQQA33P00030	30000 ⁺ 500MM
FOQQA33P00050	50000 ⁺ 500MM
FOQQA33P00100	100000 ⁺ 1000MM

TABLE 2	
ITEM NUMBER	DESCRIPTION
1	OFNP, OM3, 8 FIBER 50/125 μ M
2	PLUG, QSFP, REFERENCE SFF-8661
3	LABEL - AHSP P/N, REV, DATE CODE, LENGTH, CoO & SERIAL NUMBER
4	LANYARD - BLACK



1. UL LABEL MUST BE ON THE SHIPPING CARTON PER SUBJECT 764 OF THE UL COMPONENT WIRING HARNESS(ZPFW2) FILE#E86140. CSA LABEL MUST BE ON SHIPPING CARTON.
2. PACKAGE COMPLETED ASSY IN AN APPROPRIATELY SIZED ESD BAG.
3. EPROM CONTENT SHALL BE COMPLIANT WITH SFF-8636 SECIFICATIONS FOR 100GBASE-SR4. EPROM REVISION IS EQUAL TO ATCS PART NUMBER REVISION.
4. COMPLIANT TO EU DIRECTIVE 2011/65/EU - ROHS2.
5. ASSEMBLIES SHALL BE COMPLIANT TO INFINIBAND EDR SPECIFICATIONS.
6. THIS DRAWING IS RESERVED FOR AMPHENOL STANDARD PRODUCT.

TOLERANCES		DW	05/09/2017 TJC	Amphenol AHP A Division of Amphenol Corporation 200 Innovative Way, Suite 201, Nashua, N.H. 03062 (603) 879-3000				
0.0	± 0.1	CHK	05/09/2017					
0.00	± 0.08		DJD					
	±	AFVD	05/09/2017					
ANGLES	± 1.0°		TJC					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN mm				TITLE CABLE ASSEMBLY, QSFP TO QSFP, OM 3, OFNP, ACTIVE OPTICAL, 100Gbps				
CUSTOMER USE DRAWING								
						PART NO.		REV
						SEE TABLE 1		NA
				DRAWING NO.		REV		
				C-FOQQ-A3-3P-00999		A		
SIZE		D	SCALE	1:1	SHEET 1	OF 1		