

Terminal Part Number: 13613157
Surface Plating: SN
Material Thickness [mm]: 0,25
Cross Section [mm²]: 0,80 | 1,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office



Cable Type codes: 1005
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,85 - 2,40
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,80		2,03	90	1,20	0,05	2,05	0,10	2,40	0,10	2,50	0,10
1005 1,00		2,23	120	1,25	0,05	2,10	0,10	2,40	0,10	2,60	0,10

Cable type code legend:

1005:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, PVDF, XLPE
Insul. Wall Designator: THIN



Terminal Part Number: 13613157
Surface Plating: SN
Material Thickness [mm]: 0,25
Cross Section [mm²]: 0,80

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*


Cable Type codes: 1019
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,70 - 1,90
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1019 0,80		1,80	90	1,20	0,05	2,05	0,10	2,40	0,10	2,50	0,10

Cable type code legend:

1019:

Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE
Insul. Wall Designator: THIN SPECIAL



Terminal Part Number: 13613157

Surface Plating: SN

Material Thickness [mm]: 0,25

Cross Section [mm²]: 1,00

Cable Type codes: 1098

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 2,09 - 2,25

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1098 1,00		2,17	120	1,20	0,05	2,10	0,10	2,50	0,10	2,60	0,10

Cable type code legend:

1098:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: ETFE

Insul. Wall Designator: THIN



Terminal Part Number: 13613157
Surface Plating: SN
Material Thickness [mm]: 0,25
Cross Section [mm²]: 0,75 | 1,00

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,60 - 2,10
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,75		1,75	120	1,40	0,05	1,90	0,10	2,25	0,10	2,55	0,10
2010 1,00		1,95	160	1,45	0,05	1,95	0,10	2,35	0,10	2,65	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 13613157

Surface Plating: SN

Material Thickness [mm]: 0,25

Cross Section [mm²]: 1,25

Cable Type codes: 3004

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 2,00 - 2,20

Seal(s): NONE

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 1,25		2,10	135	1,30	0,05	2,10	0,10	2,40	0,10	2,60	0,10

Cable type code legend:

3004: AVSS

Industry Designator: JIS/JA

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, XLPE, X-PVC

Insul. Wall Designator: THIN

