

ÖLFLEX® HEAT 180 FZLSi

ÖLFLEX® HEAT 180 FZLSi - silicone single core for special use as 10 kV high-voltage ignition wire for expanded temperatures up to +180°C

Info

10 kV high-voltage ignition wire



Halogen-free



Cold-resistant



Temperature-resistant

Benefits

Possesses insulating properties after combustion due to remaining SiO₂ ash on the conductor

Application range

Areas with high ambient temperatures where conventional core insulation materials will embrittle after a short while

Typical fields of application

- Control cabinet manufacturing
- Appliances and apparatus engineering
- Electric motor industry
- Sauna/solarium construction
- Thermal and heating elements
- Lighting technology
- Ventilator engineering
- Air-conditioning technology
- Furnace construction
- Polymer processing
- Generator and transformer manufacturing

ÖLFLEX® HEAT 180 SiZ is suitable as electrical sensor cable in pipe systems for modern solar hot water systems

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 FZLSi

Product features

Halogen-free according to IEC 60754-1

(amount of halogen acid gas)

Corrosiveness of combustion gases according to IEC 60754-2 (degree of acidity)

Flame-retardant according IEC 60332-1-2

Resistant to a multitude of oils, alcohols, vegetable and animal fats and chemical substances

Adequate ventilation must be ensured, since the mechanical properties of silicone cables decrease from +100 °C in the absence of air

Norm references / Approvals

Increased voltage rating is not subject to the

Low Voltage Directive 2014/35/EU

Product Make-up

Fine-wire, tinned-copper conductor

Silicone-based insulation

Colour of core insulation: red

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000993 ETIM 5.0 Class-Description: Single core cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000993 ETIM 6.0 Class-Description: Single core cable
Conductor stranding:	Fine wire acc. to VDE 0295, class 5 / IEC 60228 class 5 from 0.5 mm ²
Minimum bending radius:	Fixed installation: 6 x core diameter One bend at end of core: 3 x cable diameter
Nominal voltage:	Version SiF/GL / SiZ: U0/U 300/500 V Version FZLSi: 10 kV
Test voltage:	Version SiF/GL / SiZ: 2000 V Version FZLSi: 20 kV
Temperature range:	-50 °C to +180 °C (adequate ventilation required) Short-term: +200 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 FZLSi

Article number	Conductor cross-section (mm ²)	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 180 FZLSi high-voltage ignition wire				
2510001	1 (32 x 0,2)	7	9.6	68
2510005	1.5 (30 x 0,25)	7.6	14.4	83

Last Update (1.1.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16