

Part Number : 2166231023
Product Description : Squba 3.6 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 600.00mm Length, Tin (Sn) Plating, 2 Circuits, Black
Series Number : 216623
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2166231023_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216623
Description	Squba 3.6 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 600.00mm Length, Tin (Sn) Plating, 2 Circuits, Black
Application	Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Squba 3.6-to-Pigtail
Keyword	Squba 3.6
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264746613

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Physical

Cable Length	600.00mm
Circuits (Loaded)	2
Circuits (maximum)	2

Downloaded from Arrow.com.

Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	21.852/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba 3.6 Sealed Receptacle Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, Black, UL1007/UL1061 Compatible	2077820002

Downloaded from Arrow.com.