



# Intel® Server System R1208SPOSHORR

☐ Add to Compare

Specifications

Essentials

- Supplemental Information
- Memory & Storage
- Processor Graphics
- Expansion Options
- I/O Specifications
- Package Specifications
- Advanced Technologies

Ordering and Compliance

Compatible Products

Downloads and Software

Essentials

Export specifications

Product Collection	Intel® Server System R1000SPO Family
Code Name	Products formerly Silver Pass
Launch Date	Q1'17
Status	Launched
Expected Discontinuance	1H'20
Limited 3-year Warranty	Yes
Extended Warranty Available for Purchase (Select Countries)	Yes
Additional Extended Warranty Details	Single Processor System Extended Warranty
Chassis Form Factor	1U Rack
Chassis Dimensions	17.26"x23.84"x1.7" (WxDxH)
Board Form Factor	uATX
Rack Rails Included	No
Compatible Product Series	Intel® Xeon® Processor E3-1200 v5 Family
Socket	LGA 1151 Socket H4
TDP	80 W
Heat Sink	F1UE3PASSHS
Heat Sink Included	Yes
System Board	Intel® Server Board S1200SP Family
Board Chipset	Intel® C236 Chipset
Target Market	Entry
Rack-Friendly Board	Yes
Power Supply	450 W
Power Supply Type	AC
# of Power Supply Included	2
Redundant Fans	No
Redundant Power Supported	Yes
Backplanes	Included

(1) Intel® Server Board S1200SPOR, (1) Riser card assembly (AXX1UPCIEX16R2), (2) 450W redundant power supply, (1) Power Distribution Board, (8) 2.5 inch Hot-swap drive bays with (8) 2.5 inch Hot-swap drive trays (FXX25HSCAR2), and (1) 12Gb SAS Backplane (F1U8X25S3HSBP), (1) SATA data cable, (1) Backplane 12C cable, (1) SATA ODD data cable, (1) SAS Data cable, (3) System fans, (1) Standard control panel assembly, (1) Front I/O Panel assembly (1 x VGA & 2 x USB), (1) SATA Optical drive bay with filler panel, (2) Chassis handles

Included  
Items

Recommended Customer Price 

N/A

## Supplemental Information

Datasheet

[View now](#)

Description

Intel® Server System R1208SPOSHORR  
 1U rack system with S1200SPOR board and 8 x 2.5 hot-swappable HDD  
 Drive cage, 2 x 450W redundant power supplies  
 Supporting one Intel® Xeon® Processor E3-1200 v5 & v6 family

Additional Information URL

[View now](#)

## Memory & Storage

Memory Types 

DDR4 ECC UDIMM

Max # of DIMMs 

4

Max Memory Size (dependent on memory type) 

64 GB

DIMM Type

UDIMM

# of Front Drives Supported

8

Front Drive Form Factor

Hot-swap 2.5"

# of Internal Drives Supported

1

Internal Drive Form Factor

M.2 SSD

## Processor Graphics

Integrated Graphics <sup>‡</sup> 

No

## Expansion Options

Connector for Intel® I/O Expansion Module x8 Gen 3 

1

Connector for Intel® Integrated RAID Module 

1

Riser Slot 1: Total # of Lanes

8

Riser Slot 1: Included Slot Configuration(s) 

1x PCIe Gen3 x8

## I/O Specifications

# of USB Ports

9

Total # of SATA Ports 

8

RAID Configuration 

Software RAID RSTe (0,1,10,5) and ESRT2 (0,1,10)

# of Serial Ports 

1

Integrated LAN 

i210

# of LAN Ports 

2

Optical Drive Support







Yes

## Package Specifications

Max CPU Configuration

1

## Advanced Technologies

Intel® Remote Management Module Support 	Yes
Integrated BMC with IPMI 	IPMI 2.0
Intel® Node Manager 	Yes
Intel® Rapid Storage Technology enterprise 	Yes
Intel® I/O Acceleration Technology 	Yes
TPM Version 	1.2

## More support options for Intel® Server System R1208SPOSHORR



Product Support



Downloads and Software



Support Community



Warranty and Replacement



Need more help?

[Contact support](#)



[Give Feedback](#)

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

Intel classifications are for informational purposes only and consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company as an importer and/or exporter is responsible for determining the correct classification of your transaction.

Refer to Datasheet for formal definitions of product properties and features.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

‡ This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VMM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers, typically represent 1,000-unit purchase quantities, and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. If sold in bulk, price represents individual unit. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.



[Company Information](#) [Our Commitment](#) [Communities](#) [Investor Relations](#) [Contact Us](#)

[Newsroom](#) [Jobs](#)



