
Fixing Ties for Weld Studs, for parallel routing

Many applications require cables to be run parallel to each other but separated to avoid abrasion. The double mounting base, when used with two cable ties allows this to be achieved simply and quickly.

Features and benefits

- Pre-assembled 2-piece fixing tie with stud retainer
- For parallel routing of cables, hoses or harnesses
- Cable tie head can be moved after bundling
- Easy to install without the need for a tool
- For 5 mm studs or 5 mm ISO threaded studs



DSBS5



Parallel fixation of two cables.

Other dimensions are available on request.


Material specification please see page 26.

2-Piece Fixing Ties for Weld Studs

TYPE	Width (W)	Length (L)	Bundle Ø max.	N	Stud Ø	Material Cable Tie	Material Foot Part	Colour	Tools	Article-No.
T50SDSBS5	4.6	150.0	35.0	225	5.0	PA66HS	PA66HIRHS	Black (BK)	2-10	150-56193
T50ROSDSBS5	4.6	200.0	45.0	222	5.0	PA66HS	PA66HIRHS	Black (BK)	2-10	150-56199

All dimensions in mm. Subject to technical changes.

1-Piece Fixing Ties for Weld Studs for Heavy Duty Applications



Dual Clamp Ties (DCT)

TYPE	Width (W)	Length (L)	Bundle Ø max.	Stud Ø	Material	Colour	Tools	Article-No.
DCT11	12.7	489.0	58.0	6.35	PA66HIRHSUV	Black (BK)	3;9-12	115-31100
DCT9	12.8	331.0	33.0	6.35	PA66HIRHS	Black (BK)	2-11	115-00034

All dimensions in mm. Subject to technical changes.

Recommended Tools											
	2 MK20	3 MK21	4 MK3SP	5 MK3PNSP2	6 EVO7	7 MK7HT	8 MK7P	9 MK6	10 EVO9	11 EVO9HT	12 MK9P
	551	551	552	552	554	555	556	557	554	554	558

For more information on toolings please refer to the Application Tooling chapter.

Date of issue: 10/2017

Downloaded from Arrow.com.

Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium-alloy	AL	-40 °C to +180 °C	Natural (NA)		• Corrosion resistant • Antimagnetic	RoHS
Chloroprene	CR	-20 °C to +80 °C	Black (BK)		• Weather-resistant • High yield strength	RoHS
Ethylene Tetrafluoroethylene (Tefzel®)	E/TFE	-80 °C to +170 °C	Blue (BU)	UL 94 V0	• Resistance to radioactivity • UV- resistant, not moisture sensitive • Good chemical resistance to: acids, bases, oxidizing agents	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL 94 HB	• Limited brittleness sensitivity • Flexible at low temperature • Not moisture sensitive • Robust on impacts	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	• Bio-plastic, derived from vegetable oil • Strong impact resistance at low temperature • Very low moisture absorption • Weather-resistant • Good chemical resistanc	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	• Good chemical resistance to: acids, bases, oxidizing agents • UV- resistant	HF RoHS
Polyamide 4.6	PA46	-40 °C to +150 °C (5000 h), +195 °C (500 h)	Natural (NA), Grey (GY)	UL 94 V2	• Resistance to high temperatures • Very moisture sensitive • Low smoke sensitiv	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL 94 V2	• High yield strength	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL 94 HB	• Limited brittleness sensitivity • Higher flexibility at low temperature	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL 94 V2	• High yield strength	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13, PA66GF15	-40 °C to +105 °C	Black (BK)	UL 94 HB	• Good resistance to: lubricants, vehicle fuel, salt water and a lot of solvent	HF RoHS
Polyamide 6.6, heat and UV stabilised	PA66HSW	-40 °C to +105 °C	Black (BK)	UL 94 V2	• High yield strength • Modified elevated max. temperature • UV-resistant	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C	Black (BK), Natural (NA)	UL 94 V2	• High yield strength • Modified elevated max. temperature	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	• Limited brittleness sensitivity • Higher flexibility at low temperature	RoHS
Polyamide 6.6, high impact modified, heat and UV stabilised	PA66HIRHSW	-40 °C to +110 °C	Black (BK)	UL 94 HB	• Limited brittleness sensitivity • Higher flexibility at low temperature • Modified elevated max. temperature • High yield strength, UV-resistant	RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C	Black (BK)	UL 94 HB	• Limited brittleness sensitivity • Higher flexibility at low temperature • Modified elevated max. temperature	RoHS
Polyamide 6.6, high impact modified, ScanBlack	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	• Limited brittleness sensitivity • Higher flexibility at low temperature	RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 V2	• High yield strength • UV-resistant	HF RoHS

Date of issue: 10/2017

Downloaded from Arrow.com.

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6, with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL 94 HB	• High yield strength • Metal and X-Ray detectable	HF RoHS
Polyamide 6.6, with metal particles	PA66MP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	• High yield strength • Metal and x-ray detectable	HF RoHS
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL 94 V0	• High yield strength • Low smoke emission	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)	halogen free	• UV-resistant • Good chemical resistance to: most acids, alkaliks and oils	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL 94 V0	• Resistance to radioactivity • Not moisture sensitive • Good chemical resistance to: acids, bases, oxidizing agents	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL 94 HB	• Low moisture absorption • Good chemical oilsresistance to: most acids, alcohol and oils	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL 94 V0	• Low smoke emissions	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL 94 HB	• Floats in water • Moderate yield strength • Good chemical resistance to: organic acids	HF RoHS
Polypropylene, Ethylene-Propylene-Dien-Terpolymere-rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL 94 HB	• Good resistance to high temperatures • Good chemical and abrasion resistance	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL 94 HB	• Metal and X-Ray detectable • Heat resistant • Moderate yield strength • Good chemical resistance	RoHS
Polypropylene with metal particles	PPMP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	• High yield strength • Metal and x-ray detectable	HF RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL 94 V0	• Low moisture absorption • Good chemical resistance to: acids, ethanol and oil	RoHS
Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	non-burning	• Corrosion resistant • Antimagnetic • Weather resistant • Outstanding chemical resistance	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL 94 HB	• High elastic • Good chemical resistance to: acids, bases and oxidizing agents	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In additon to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers.
*These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

**More colours on request.

N = **Minimum Loop Tensile Strength for Cable Ties (Newton)**

HF = Halogenfree
LFH = Limited Fire Hazard
RoHS = Restriction of Hazardous Substances

Date of issue: 10/2017

Downloaded from Arrow.com.