LITE-ON SEMICONDUCTOR

TB0080ML

SURFACE MOUNT
THYRISTOR SURGE PROTECTIVE DEVICE

Bi-Directional

VDRM - **6** Volts
IPP - **80** Amperes


FEATURES

- Bidirectional protection in a single device
- High off state Impedance and low on state voltage
- Surge capabilities up to 80A @10/1000us or 250A @8/20us
- Low Capacitance
- Plastic material has UL flammability classification 94V-0
- Qualified to AEC-Q101 Rev_C

MECHANICAL DATA

- Case : Molded plastic
- Polarity : Denotes none cathode band
- Weight : 0.003 ounces, 0.093 grams

SMB



SMB		
DIM.	MIN.	MAX.
A	4.06	4.57
B	3.30	3.94
C	1.96	2.21
D	0.15	0.31
E	5.21	5.59
F	0.05	0.20
G	2.01	2.62
H	0.76	1.52
All Dimensions in millimeter		

MAXIMUM RATINGS


CHARACTERISTICS	SYMBOL	VALUE	UNIT
Non-repetitive peak impulse current @ 10/1000us	IPP	80	A
Junction temperature range	TJ	-40 to +150	℃
storage temperature range	TSTG	-55 to +150	℃

THERMAL RESISTANCE

CHARACTERISTICS	SYMBOL	VALUE	UNIT
Junction to leads	Rth(J-L)	20	℃ /W
Junction to ambient on print circuit (on recommended pad layout)	Rth(J-A)	100	℃ /W
Typical positive temperature coefficient for brekdown voltage	△ VBR/△ TJ	0.1	%/℃

MAXIMUM RATED SURGE WAVEFORM

WAVEFORM	STANDARD	IPP (A)
2/10 us	GR-1089-CORE	250
8/20 us	IEC 61000-4-5	250
10/160 us	FCC Part 68	150
10/560 us	FCC Part 68	100
10/700 us	ITU-T K20/K21	100
10/1000 us	GR-1089-CORE	80




REV. 0, Aug-2016, KSWB10

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS @ T_A= 25℃ unless otherwise specified
TB0080ML

PARAMETER	MARKING CODE	RATED REPETITIVE OFF-STATE VOLTAGE	OFF-STATE LEAKAGE CURRENT @ V_{DRM}	BREAKOVER VOLTAGE	ON-STATE VOLTAGE @ I_T=2.2A	BREAKOVER CURRENT		HOLDING CURRENT		OFF-STATE CAPACITANCE
SYMBOL		V_{DRM}	I_{DRM}	V_{BO}	V_T	I_{BO}		I_H		Co
UNITS		Volts	uA	Volts	Volts	mA		mA		pF
LIMIT		Max	Max	Max	Max	Min	Max	Min	Max	Typ
TB0080ML	T008ML	6	5	25	4	50	800	50	250	21

SYMBOL	PARAMETER	
V_{DRM}	Stand-off Voltage	
I_{DRM}	Leakage current at stand-off voltage	
V_{BR}	Breakdown voltage	
I_{BR}	Breakdown current	
V_{BO}	Breakover voltage	
I_{BO}	Breakover current	
I_H	Holding current	Note: 1
V_T	On state voltage	
I_{PP}	Peak pulse current	
Co	Off state capacitance	Note: 2



NOTES: 1. I_H > (V_L/R_L) If this criterion is not obeyed, the T_{SPD} Triggers but does not return correctly to high-resistance state. The Surge recovery time does not exceed 30ms.
2. Off-state capacitance measured at f=1.0MHz; 1.0V_{RMS} signal; VR=2V_{DC} bias.

Downloaded from Arrow.com.

RATING AND CHARACTERISTICS CURVES
TB0080ML

FIG.1-OFF STATE CURRENT VS JUNCTION TEMPERATURE




FIG.2-RELATIVE VARIATION OF BREAKDOWN VOLTAGE VS JUNCTION TEMPERATURE




FIG.3-RELATIVE VARIATION OF BREAKDOWN VOLTAGE VS JUNCTION TEMPERATURE




FIG.4-ON STATE CURRENT VS ON STATE VOLTAGE




FIG.5-RELATIVE VARIATION OF HOLDING CURRENT VS JUNCTION TEMPERATURE








FIG.6-RELATIVE VARIATION OF JUNCTION CAPACITANCE VS REVERSE VOLTAGE BIAS



Downloaded from Arrow.com.







The PTC (Positive Temperature Coefficient) is an overcurrent protection device

Downloaded from Arrow.com.

Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.

Downloaded from Arrow.com.