



105PPB102K

HIGH DVDT/ PULSE
Parts are RoHS compliant

APPLICATIONS: SNUBBER, SCR commutation, TV deflection circuits

ELECTRICAL SPECIFICATIONS

Capacitance: 1 μ F

Dissipation Factor: 0.0004 Max at 1000 Hz and 25°C , 0.0006 Max at 10 kHz and 25°C

Temperature Coefficient: -200 PPM/°C, -100 PPM/°C, 100 PPM/°C

Ripple Current: at and

ESR: - at - and -

Self Inductance: 1 Nanohenries maximum per mm of pitch

dvdt: 1200 V/ μ s

Tolerance: -10 % , +10 %

Temperature Range: -55°C to +105°C

Above 85°C the rated (DC/AC) voltage must be derated at per 1.25%/2.25%°C

WVDC: 1000 Volts DC

SVDC: N/A Volts DC

VAC: 600 Volts AC

Terminal to Terminal Dielectric strength: 1.6 times the rated DC voltage when applied between the terminals for 10 seconds

Terminal to case Dielectric strength: 13.6 VAC when applied between the terminals and case for 60 seconds

Insulation Resistance (Terminal to Terminal): 30000 MINIMUM after 100 Volts DC is applied for 60 seconds at 20°C

Insulation resistance (Terminal to Case): N/A Megohms MINIMUM after 0 Volts DC is applied for 0 seconds at 0

Reliability: 1 FIT

Load Life: 2000 hours at 85°C with 125% of rated voltage

Capacitance Change: $\leq$ 1% of initially measured value

D.F. Change: .001 of maximum specified value

I.R. Change: $>$ 50% of minimum specified value

PHYSICAL DIMENSIONS

Length (L): 42.5 mm, 0.8 mm


Height (H): 37 mm, $\pm$ 0.8 mm

Thickness (T): 28 mm, $\pm$ 0.6 mm

Lead Spacing (S): 37.5 mm, $\pm$ 0.4 mm

Lead Diameter (d): 1 mm, $\pm$ 0.05 mm

Lead Length (LL): 30.0mm, $\pm$ 5 mm



2400 East Devon Avenue Suite 292 Des Plaines, IL 60018 (847) 675-1760 FAX (847) 673-2850

Illinois Capacitor (HK) Ltd., Tel: 85227930931, Fax: 85227930731, www.illcap.com.hk

© Copyright 2020 Illinois Capacitor. An affiliate of Cornell Dubilier, All Rights Reserved