

CGJ5L2C0G1H683J160AA

TDK Item Description : CGJ5L2C0G1H683JT***




Application & Main Feature

High Reliability Grade (General (Up to 50V))

Series

CGJ5(3216) [EIA CC1206]



Dimensions

L 3.20mm +/-0.2mm
W 1.60mm +/-0.2mm
T 1.60mm +/-0.2mm
B 0.20mm Min.
G 1.00mm Min.

Temperature Characteristic

C0G (-55 to 125 degC 0+/-30ppm/degC)

Rated Voltage

1H (50Vdc)

Capacitance

68nF

Capacitance Tolerance

J (+/-5%)

O Factor

1000 Min.


Insulation Resistance

7.35Gohm Min.


AEC-Q200

Yes


|Z|, ESR vs. Freq. Characteristics



DC Bias Characteristic



Cap. vs. Freq. Characteristic



Temperature Characteristics

