

HONEYWELL PART NUMBER
11SX37-T
PRODUCT CODE
VDJ2186

REV	DOCUMENT	CHANGED BY	CHECK
5	0038448	VS 28APR08	BLR



B

A

A

B

A



NOTE --
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING
3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO.	PR-7928
REPLACES	

CHARACTERISTICS	ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	12FEB08	Honeywell			
OPERATING FORCE — — — 2.5-5 OZ MAX	CONTACT ARRANGEMENT S P D T							CHECK	RJ	12FEB08				
RELEASE FORCE— — — — 1 OZ MIN		28 VOLTS DC RATING		115 VOLTS AC, 60 CPS		0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .001 MAX		SEA LEVEL	50,000 FT	SEA LEVEL										
OVERTRAVEL — — — — — .004 MIN	INDUCTIVE	3 AMP	2 AMP	5 AMP			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
	RESISTIVE	5 AMP	4 AMP	5 AMP						B	I	11SX37-T		5
	-						RASTER			SCALE	-	WEIGHT:.003 LB MAX		SHEET 1 OF 1
	APPROVALS	KEMA, CE	5A 250 V ~ T125 5E4 											
		UL, CSA	5A 250 VAC   BRAND L4L											