



Color:  white Similar to illustration

| Technical data              |  |                                          |
|-----------------------------|--|------------------------------------------|
| Suitable                    |  | for WAGO Rail-Mount Terminal Blocks      |
| Marking method              |  | Thermal transfer                         |
| Marking                     |  | plain                                    |
| Delivery form               |  | Roll                                     |
| Delivery form configuration |  | 2,300 WMB markers (3.5 mm)/reel          |
| Flammability class per UL94 |  | V2                                       |
| Printing device             |  | Smart Printer (thermal transfer printer) |

| Physical data      |  |        |
|--------------------|--|--------|
| Marker/strip width |  | 3.5 mm |
| Marker width       |  | 3.5 mm |

| Mechanical data  |  |                                         |
|------------------|--|-----------------------------------------|
| Smear resistance |  | in conjunction with 258-5005 Ink Ribbon |

| Material data |  |                               |
|---------------|--|-------------------------------|
| Color         |  | white                         |
| UV resistance |  | EN 60068-2-5:2010 Procedure B |
| Halogen-free  |  | Yes                           |
| Weight        |  | 125.8 g                       |
| Fire load     |  | 2.415 MJ                      |

## Environmental requirements

### Environmental Testing

|                                                                                                     |                                                     |
|-----------------------------------------------------------------------------------------------------|-----------------------------------------------------|
| Test specification:<br>Railway applications –<br>Rolling stock –<br>Electronic equipment            | DIN EN 50155 (VDE 0115-200):2022-06                 |
| Test procedure:<br>Railway applications –<br>Rolling stock equipment –<br>Vibration and shock tests | DIN EN 61373 (VDE 0115-0106):2011-04                |
| Spectrum/Mounting location                                                                          | Service life test, Category 1, Class A/B            |
| Functional test with noise-like oscillations                                                        | Test passed according to Section 8 of the standard  |
| Frequency                                                                                           | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$      |
| Acceleration                                                                                        | 0.101g (highest test level used for all axes)       |
| Test duration per axis                                                                              | 10 min.                                             |
| Test directions                                                                                     | X, Y and Z axes                                     |
| Monitoring of contact faults and interruptions                                                      | Passed                                              |
| Voltage drop measurement before and after each axis                                                 | Passed                                              |
| Simulated service life test through increased levels of noise-like oscillations                     | Test passed according to Section 9 of the standard  |
| Frequency                                                                                           | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$      |
| Acceleration                                                                                        | 0.572g (highest test level used for all axes)       |
| Test duration per axis                                                                              | 5 h                                                 |
| Test directions                                                                                     | X, Y and Z axes                                     |
| Extended testing: Monitoring of contact faults and interruptions                                    | Passed                                              |
| Extended testing: Voltage drop measurement before and after each axis                               | Passed                                              |
| Shock test                                                                                          | Test passed according to Section 10 of the standard |
| Shock pulse form                                                                                    | Half sine                                           |
| Acceleration                                                                                        | 5g (highest test level used for all axes)           |
| Shock duration                                                                                      | 30 ms                                               |
| Number of shocks (per axis)                                                                         | 3 pos. und 3 neg.                                   |
| Test directions                                                                                     | X, Y and Z axes                                     |
| Extended testing: Monitoring of contact faults and interruptions                                    | Passed                                              |
| Extended testing: Voltage drop measurement before and after each axis                               | Passed                                              |
| Vibration and shock stress for rolling stock equipment                                              | Passed                                              |

### Commercial data

|                       |               |
|-----------------------|---------------|
| PU (SPU)              | 1 pcs         |
| Packaging type        | Bag           |
| Country of origin     | DE            |
| GTIN                  | 4055143361309 |
| Customs tariff number | 39269097900   |

| Product Classification |                      |
|------------------------|----------------------|
| UNSPSC                 | 55121612             |
| eCl@ss 10.0            | 27-14-11-37          |
| eCl@ss 9.0             | 27-14-11-37          |
| ETIM 9.0               | EC000761             |
| ETIM 10.0              | EC000761             |
| ECCN                   | NO US CLASSIFICATION |

| Environmental Product Compliance |                         |
|----------------------------------|-------------------------|
| RoHS Compliance Status           | Compliant, No Exemption |

Approvals / Certificates

Declarations of conformity and manufacturer's declarations



| Approval                      | Standard | Certificate Name |
|-------------------------------|----------|------------------|
| Railway<br>WAGO GmbH & Co. KG | -        | Railway Ready    |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2009-113

↓

| Documentation |            |                                           |                 |
|---------------|------------|-------------------------------------------|-----------------|
| Bid Text      |            | Operating Instructions                    |                 |
| 2009-113      | 19.02.2019 | xml<br>2.54 KB                            | ↓               |
| 2009-113      | 04.01.2018 | doc<br>23.50 KB                           | ↓               |
|               |            | 2009-115 Information on printing material | 1<br>28.08.2020 |
|               |            | pdf<br>1230.84 KB                         | ↓               |

| CAD/CAE-Data          |                            |
|-----------------------|----------------------------|
| CAD data              | CAE data                   |
| 2D/3D Models 2009-113 | EPLAN Data Portal 2009-113 |
| ↓                     | ↓                          |
|                       | ZUKEN Portal 2009-113      |
|                       | ↓                          |

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Accessories for marking devices




Item No.: 258-5007  
Roller; for Smart Printer; for WMB-Inline WA-  
GO (2009-115, -114, -113); 1 grinding device

Installation Notes

Application



Separating an individual marker from the  
WMB marker strip – for larger terminal  
blocks.



Snapping a marking strip into the marker  
slot.

Marking



Snapping a WMB marker strip into the mark-  
er slot of the double marker carrier.



Snapping a marking strip into the marker  
slot.