



IZLT2.E101405 Fuseholders, Cartridge Fuse - Component

If you notice a change to your IZLT2 Listing Card, click [here](#) to learn more.

[Page Bottom](#)

Fuseholders, Cartridge Fuse - Component

[See General Information for Fuseholders, Cartridge Fuse - Component](#)

SATO PARTS CO LTD

E101405

3F SANYU BLDG.

3-42-1 HONGO

BUNKYO-KU, TOKYO 113-0033 JAPAN

Cat. No.	Voltage Rating (V)	Current Rating (A)	Withstand Rating RMS Symmetrical	Fuse Class or Size
F 105	250ac/dc	10	-	5.2 mm diameter by 20 mm long
F-100	250ac/dc	10	-	20 mm by 5.2 mm diameter
F-110	250ac/dc	10	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-115	250ac/dc	6	-	5.2 mm diameter by 20 mm long
F-120-A	250ac/dc	10	-	6.4 mm diameter by 31.8 mm long
F-120-B	250ac/dc	10	-	6.4 mm diameter by 31.8 mm long
F-130	250ac/dc	10	-	6.4 mm diameter by 31.8 mm long
F-200-N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-200N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-240-N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-240N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-300-1P	250ac/dc	5	-	5 mm diameter by 20 mm long
F-300-2P	250ac/dc	5	-	5 mm diameter by 20 mm long
F-300-3P	250ac/dc	5	-	5 mm diameter by 20 mm long
F-33L	250ac/dc	8	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-33S	250ac/dc	6	-	20 mm by 5.2 mm diameter
F-400-01A1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-400-01A2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-400-01B1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-400-01B2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-4000-A	250ac/dc	10	-	6.4 mm diameter by 30 mm long
F-4000-B	250ac/dc	10	-	6.4 mm diameter by 30 mm long
F-450	300ac/dc	25	-	6.4mm diameter by 30 mm long or 6.35mm diameter by 30 mm long
F-500-01A1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-500-01A2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-500-01B1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-500-01B2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-60-A	125ac/dc	5	-	5.2 mm diameter by 20 mm long

F-60-B	125ac/dc	5	-	5.2 mm diameter by 20 mm long
F-60-C	125ac/dc	5	-	5.2 mm diameter by 20 mm long
F-600	250ac/dc	8	-	5.2 mm diameter by 20 mm long
F-61-A	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-61-B	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-61-C	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-61-D	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-610	250ac/dc	8	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-64-AB	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-64-AD	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-64-BB	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-64-BD	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-65-AB	250ac/dc	10	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-65-AD	250dc	10	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-65-BB	250ac/dc	10	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-65-BD	250ac/dc	10	-	31.8 mm by 6.35 mm diameter or 30 mm by 6.4 mm diameter
F-66-AD	250ac/dc	10	-	38.1 mm by 10.31 mm diameter
F-66-AF	250ac/dc	20	-	38.1 mm by 10.31 mm diameter
F-66-BD	250ac/dc	20	-	38.1 mm by 10.31 mm diameter
F-66-BF	250ac/dc	20	-	38.1 mm by 10.31 mm diameter
F-70	250ac/dc	30	-	31.8 mm by 6.35 mm diameter
F-700 may be followed by -A or -B, may be followed by L, may be followed by -2P to 30P				
	250ac/dc	10	-	6.4mm diameter by 30 mm long, 6.35mm diameter by 30 mm long or 6.35 mm diameter by 31.8mm long
F-710 may be followed by -A or -B, may be followed by -2P to -30P	250ac/dc	10	-	5.2 mm diameter by 20 mm
F-720 may be followed by -L, may be followed by -2P to -30P	250ac/dc	20	-	10.3 mm diameter by 38.0 mm long
F-75	250ac/dc	10	-	20 mm by 5.2 mm diameter
F-750 may be followed by -2P to -30P	250ac/dc	15	-	6.4mm diameter by 30 mm long,
F-85	250ac/dc	10	-	31.8 mm by 6.35 mm diameter

Marking: Company name or tradename "SATO PARTS" and model designation.

Last Updated on 2017-10-29

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

↗ 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".



IZLT2.GuideInfo Fuseholders, Cartridge Fuse - Component

[View Listings](#)[Page Bottom](#)

[Fuseholders - Component] Fuseholders, Cartridge Fuse - Component

[See General Information for Fuseholders - Component](#)

The devices covered under this category are incomplete in certain constructional features or restricted in performance capabilities and are intended for use as components of complete equipment submitted for investigation rather than for direct separate installation in the field. THE FINAL ACCEPTANCE OF THE COMPONENT IS DEPENDENT UPON ITS INSTALLATION AND USE IN COMPLETE EQUIPMENT SUBMITTED TO UL.

USE

This category covers fuseholders intended for use with Class CC, G, H, J, K, R, T, special-purpose and supplementary cartridge fuses, and intended for installation in end-use equipment or products.

CONDITIONS OF ACCEPTABILITY

Consideration is to be given to the Conditions of Acceptability specified in the individual Recognitions when these components are employed in the end-use equipment.

RELATED PRODUCTS

Fuseholders intended to accept supplementary fuses (miscellaneous, miniature and micro) may additionally be covered under Terminal Blocks ([XCFR2](#)).

REQUIREMENTS

The basic standard used to investigate products in this category is [ANSI/UL 4248-1](#), "Fuseholders - Part 1: General Requirements," in addition to one of the following as applicable:

[ANSI/UL 4248-4](#), "Fuseholders - Part 4: Class CC"

[ANSI/UL 4248-5](#), "Fuseholders - Part 5: Class G"

[ANSI/UL 4248-6](#), "Fuseholders - Part 6: Class H"

[ANSI/UL 4248-8](#), "Fuseholders - Part 8: Class J"

[ANSI/UL 4248-9](#), "Fuseholders - Part 9: Class K"

[ANSI/UL 4248-12](#), "Fuseholders - Part 12: Class R"

[ANSI/UL 4248-15](#), "Fuseholders - Part 15: Class T"

UL, in performing its functions in accordance with its objectives, does not assume or undertake to discharge any responsibility of the manufacturer or any other party. UL shall not incur any obligation or liability for any loss, expense or damages, including incidental or consequential damages, arising out of or in connection with the use, interpretation of, or reliance upon this Guide Information.

[Last Updated](#) on 2010-03-05

[Questions?](#)[Print this page](#)[Terms of Use](#)[Page Top](#)

↗ 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".



IZLT8.E101405 Fuseholders, Cartridge Fuse Certified for Canada - Component

If you notice a change to your IZLT8 Listing Card, click [here](#) to learn more.

[Page Bottom](#)

Fuseholders, Cartridge Fuse Certified for Canada - Component

See General Information for Fuseholders, Cartridge Fuse Certified for Canada - Component

SATO PARTS CO LTD


E101405

3F SANYU BLDG.

3-42-1 HONGO

BUNKYO-KU, TOKYO 113-0033 JAPAN

Cat. No.	Voltage Rating (V)	Current Rating (A)	Withstand Rating RMS Symmetrical	Fuse Class or Size
F-115	250ac/dc	6	-	5.2 mm diameter by 20 mm long
F-200-N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-200N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-240-N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-240N	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-400-01A1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-400-01A2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-400-01B1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-400-01B2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-4000-A	250ac/dc	10	-	6.4 mm diameter by 30 mm long
F-4000-B	250ac/dc	10	-	6.4 mm diameter by 30 mm long
F-450	300ac/dc	25	-	6.4mm diameter by 30 mm long or 6.35mm diameter by 30 mm long
F-500-01A1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-500-01A2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-500-01B1	250ac/dc	10	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-500-01B2	250ac/dc	10	-	5.2 mm diameter by 20.0 mm long
F-600	250ac/dc	8	-	5.2 mm diameter by 20 mm long
F-610	250ac/dc	8	-	6.35 mm diameter by 31.8 mm long or 6.4 mm diameter by 30 mm long
F-700 may be followed by -A or -B, may be followed by L, may be followed by -2P to 30P				
	250ac/dc	10	-	6.4mm diameter by 30 mm long, 6.35mm diameter by 30 mm long or 6.35 mm diameter by 31.8mm long
F-710 may be followed by -A or -B, may be followed by -2P to -30P	250ac/dc	10	-	5.2 mm diameter by 20 mm
F-720 may be followed by -L, may be followed by -2P to -30P	250ac/dc	20	-	10.3 mm diameter by 38.0 mm long
F-750 may be followed by -2P to -30P	250ac/dc	15	-	6.4mm diameter by 30 mm long,

Marking: Company name or tradename "SATO PARTS" , model designation and the Recognized Component Mark for Canada,  .
Last Updated on 2017-10-29

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

↗ 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".



IZLT8.GuideInfo Fuseholders, Cartridge Fuse Certified for Canada - Component

[View Listings](#)[Page Bottom](#)

[Fuseholders Certified for Canada - Component] Fuseholders, Cartridge Fuse Certified for Canada - Component

[See General Information for Fuseholders Certified for Canada - Component](#)

The devices covered under this category are incomplete in certain constructional features or restricted in performance capabilities and are intended for use as components of complete equipment submitted for investigation rather than for direct separate installation in the field. THE FINAL ACCEPTANCE OF THE COMPONENT IS DEPENDENT UPON ITS INSTALLATION AND USE IN COMPLETE EQUIPMENT SUBMITTED TO UL.

USE

This category covers fuseholders for Type CC, G, H, J, K, R, T and HRC fuses, special-purpose fuses, supplementary fuses, rejectors for Type C fuses, and adapters for Type S fuses, and intended for installation in end-use equipment or products.

CONDITIONS OF ACCEPTABILITY

Consideration is to be given to the Conditions of Acceptability specified in the individual Recognitions when these components are employed in the end-use equipment.

RELATED PRODUCTS

Fuseholders intended to accept supplementary fuses (miscellaneous, miniature and micro) may additionally be covered under Terminal Blocks Certified for Canada ([XCFR8](#)).

REQUIREMENTS

The basic standard used to investigate products in this category is CSA-C22.2 No. 4248.1, "Fuseholders - Part 1: General Requirements," in addition to one of the following as applicable:

- CSA-C22.2 No. 4248.4, "Fuseholders - Part 4: Class CC"
- CSA-C22.2 No. 4248.5, "Fuseholders - Part 5: Class G"
- CSA-C22.2 No. 4248.6, "Fuseholders - Part 6: Class H"
- CSA-C22.2 No. 4248.8, "Fuseholders - Part 8: Class J"
- CSA-C22.2 No. 4248.9, "Fuseholders - Part 9: Class K"
- CSA-C22.2 No. 4248.12, "Fuseholders - Part 12: Class R"
- CSA-C22.2 No. 4248.15, "Fuseholders - Part 15: Class T"

UL MARKING

Components Recognized under UL's Component Recognition Program are identified by markings consisting of the Recognized company's identification and catalog, model, or other product designation. In addition, components produced under the UL Component Recognition Program

will also bear the Recognized Component Mark for Canada 

The Listing or Classification Mark of UL is not authorized for use on, or in connection with, Recognized Components. Only those components that actually bear the "Marking" should be considered as being covered under the Component Recognition Program.

UL, in performing its functions in accordance with its objectives, does not assume or undertake to discharge any responsibility of the manufacturer or any other party. UL shall not incur any obligation or liability for any loss, expense or damages, including incidental or consequential damages, arising out of or in connection with the use, interpretation of, or reliance upon this Guide Information.

[Last Updated](#) on 2010-03-05

[Questions?](#)[Print this page](#)[Terms of Use](#)[Page Top](#)

↗ 2017 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2017 UL LLC".