



**Part Number :** [351500393](#)

**Product Description :** VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow

**Series Number :** 35150

**Status :** Active

**Product Category :** Connector Accessories



---

## Documents and Resources

### Drawings

[351500393 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)


[PK-35150-003-001.pdf](#)

[PS-35150-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	35150
Description	VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow
Component Type	Terminal Position Assurance (TPA)
Product Name	VersaBlade
UPC	800754834476

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Yellow
Lock to Mating Part	Yes
Material - Resin	Nylon

Net Weight	0.393/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

## Mates With / Use With

### Use with Part(s)

Description	Part Number
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural	<u>351500300</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Blue	<u>351500304</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500309</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural	<u>351500310</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue	<u>351500314</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Natural, Glow-Wire Capable	<u>351500319</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural	<u>351500600</u>
VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500609</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural	<u>351500610</u>
VersaBlade Hybrid Receptacle	<u>351500614</u>

Housing, with Mounting Ears, 6 Circuits, Blue	
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Natural, Glow-Wire Capable	<u>351500619</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Yellow, Glow-Wire Capable	<u>351503319</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Yellow, Glow-Wire Capable	<u>351503619</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 3 Circuits, Blue, Glow-Wire Capable	<u>351504319</u>
VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue, Glow-Wire Capable	<u>351504619</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural	<u>351510310</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue	<u>351510314</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510319</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Natural	<u>351510610</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Blue	<u>351510614</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510619</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>351513619</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514319</u>
VersaBlade Multi-Module 2-3-4	<u>2026500909</u>

Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

---

This document was generated on Jun 03, 2026