

CATALOG LISTING
BME6-2RQ273

FED. MFG. CODE 91929


ISSUE	M	CATALOG LISTING	BME6-2RQ273	REPLACES

REVISIONS	
A	CO81513E
J A K	
24 FEB 97	
B	0016894
KRB	
10 NOV 05	


[illegible]

DDM/CAD

J A M 19 AUG 93	CHECK S A V 20 AUG 93	CHECK RJ	10 NOV 05	CHECK	RELEASE NO. PR-20733	REPLACES
-----------------	-----------------------	----------	-----------	-------	----------------------	----------



ROLLER LEVER MAY BE POSITIVELY LOCKED AT INTERVALS OF APPROXIMATELY 0.2° WITHIN A RANGE OF 225° (1238 POSITIONS)



NOTES

- 1 - 3X 6-32 UNC X (.219) BINDING HEAD TERMINAL SCREW AND CUPWASHER
- 2 - ROLLER LEVER BRACKET ASSEMBLY MAY BE SET AT ANY ONE OF EIGHT POSITIONS SPACED 45° APART
- 3 - FURNISHED UNASSEMBLED
- 4 - **SEAL RATING: NEMA1**
IP40

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS

OPERATING FORCE	— — — — —	10-18 OZ
RELEASE FORCE	— — — — —	6 OZ MIN
PRETRAVEL	— — — — —	.188 MAX
DIFFERENTIAL TRAVEL	— — — — —	.006 MAX
OVERTRAVEL	— — — — —	.219 MIN
SWITCH - BASIC REPLACEMENT	---	BM-2RQ66


ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L268 22A 125, 250, 480 VAC
1/2A 125 VDC, 1/4A 250 VDC



THIRD ANGLE PROJECTION



SCALE	FULL
-------	------

DO NOT SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT	.70 LB
--------	--------