



Part Number : [1301530279](#)

Product Description : Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Flying Leads (Primary), Y-Splice to (2) NEMA 5-20 Watertite Extreme Receptacles (Secondary), 20A, 120V, 12/3 SOOW Cord, 6.10m (20') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Number : 20052-Y-20MH



Documents & Resources

Drawings

[1301530279_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Flying Leads (Primary), Y-Splice to (2) NEMA 5-20 Watertite Extreme Receptacles (Secondary), 20A, 120V, 12/3 SOOW Cord, 6.10m (20') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78172561324

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V, 240V

Physical

Cord Diameter	15.11mm (.595")
Cord Grip Body Size	N/A
Cord Length	6.10m (20.0')
Cord Type	12/3 SOOW

Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	3103.479/g
Number of Receptacles	2 - Y-Splice
Packaging Type	Carton
Receptacle Type	GFCI Dual

This document was generated on Apr 22, 2025