

## M12-L fem. 5p A-cod. with conduit M17x1



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 812 2511
Specification	M12-L fem. 5p A-cod. with conduit M17x1
HARTING eCatalogue	<a href="https://harting.com/21038122511">https://harting.com/21038122511</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Element	Cable connector
Specification	with conduit Straight

### Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded
Number of contacts	4 5
Coding	A-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.14 ... 0.75 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	48 V AC 60 V DC
Rated impulse voltage	1.5 kV



Pushing Performance  
Since 1945

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.5 ... 8.8 mm
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	1
----------------	---



**Pushing Performance**  
Since 1945

## Commercial data

Net weight	46.95 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140139565
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413