Silicon Carbide (SiC) MOSFET – EliteSiC, 80 mohm, 1200 V, M1, TO-247-3L

NTHL080N120SC1A

$V_{(BR)DSS}$	$R_{DS(on)}$ MAX	I_D MAX
1200 V	110 mΩ @ 20 V	31 A


Features


- Typ. $R_{DS(on)}$ = 80 mΩ
- Ultra Low Gate Charge (typ. $Q_{G(tot)}$ = 56 nC)
- Low Effective Output Capacitance (typ. C_{oss} = 80 pF)
- 100% UIL Tested
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb−Free 2LI (on second level interconnection)

Typical Applications

- UPS
- DC−DC Converter
- Boost Inverter


N−CHANNEL MOSFET





TO−247−3LD
CASE 340CX

MARKING DIAGRAM



A = Assembly Location
YWW = Data Code (Year & Week)
ZZ = Assembly Lot
NTHL080N120SC1A = Specific Device Code

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain−to−Source Voltage			V_{DSS}	1200	V
Gate−to−Source Voltage			V_{GS}	−15/+25	V
Recommended Operation Values of Gate−to−Source Voltage	T_C < 175°C		V_{GSop}	−5/+20	V
Continuous Drain Current $R_{\theta JC}$	Steady State	T_C = 25°C	I_D	31	A
Power Dissipation $R_{\theta JC}$			P_D	178	W
Continuous Drain Current $R_{\theta JC}$	Steady State	T_C = 100°C	I_D	22	A
Power Dissipation $R_{\theta JC}$			P_D	89	W
Pulsed Drain Current (Note 2)	T_A = 25°C		I_{DM}	132	A
Operating Junction and Storage Temperature Range			T_J, T_{stg}	−55 to +175	°C
Source Current (Body Diode)			I_S	18	A
Single Pulse Drain−to−Source Avalanche Energy ($I_{L(pk)}$ = 18.5 A, L = 1 mH) (Note 3)			E_{AS}	171	mJ

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction−to−Case (Note 1)	$R_{\theta JC}$	0.84	°C/W
Junction−to−Ambient (Note 1)	$R_{\theta JA}$	40	°C/W

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Repetitive rating, limited by max junction temperature.
3. E_{AS} of 171 mJ is based on starting T_J = 25°C; L = 1 mH, I_{AS} = 18.5 A, V_{DD} = 120 V, V_{GS} = 18 V.

ORDERING INFORMATION

Device	Package	Shipping
NTHL080N120SC1A	TO−247−3LD	30 Units / Tube

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA	1200	–	–	V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$	I_D = 1 mA, referenced to 25°C	–	700	–	mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{GS} = 0 V, V_{DS} = 1200 V, T_J = 25°C	–	–	100	μA
		V_{GS} = 0 V, V_{DS} = 1200 V, T_J = 175°C	–	–	1	mA
Gate−to−Source Leakage Current	I_{GSS}	V_{GS} = +25/−15 V, V_{DS} = 0 V	–	–	±1	μA
ON CHARACTERISTICS						
Gate Threshold Voltage	$V_{GS(th)}$	V_{GS} = V_{DS}, I_D = 5 mA	1.8	2.7	4.3	V
Recommended Gate Voltage	V_{GOP}		−5	–	+20	V
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 20 V, I_D = 20 A, T_J = 25°C	–	80	110	mΩ
		V_{GS} = 20 V, I_D = 20 A, T_J = 150°C	–	114	–	
Forward Transconductance	g_{FS}	V_{DS} = 20 V, I_D = 20 A	–	13	–	S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance	C_{ISS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 800 V	–	1112	–	pF
Output Capacitance	C_{OSS}		–	80	–	
Reverse Transfer Capacitance	C_{RSS}		–	6.5	–	
Total Gate Charge	$Q_{G(tot)}$	V_{GS} = −5/20 V, V_{DS} = 600 V, I_D = 20 A	–	56	–	nC
Gate−to−Source Charge	Q_{GS}		–	11	–	
Gate−to−Drain Charge	Q_{GD}		–	12	–	
Gate Resistance	R_G	f = 1 MHz	–	1.7	–	Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(on)}$	V_{GS} = −5/20 V, V_{DS} = 800 V, I_D = 20 A, R_G = 4.7 Ω, Inductive Load	–	13	–	ns
Rise Time	t_r		–	20	–	
Turn−Off Delay Time	$t_{d(off)}$		–	22	–	
Fall Time	t_f		–	10	–	
Turn-On Switching Loss	E_{ON}		–	258	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	52	–	
Total Switching Loss	E_{TOT}		–	311	–	
DRAIN−SOURCE DIODE CHARACTERISTICS						
Continuous Drain−to−Source Diode Forward Current	I_{SD}	V_{GS} = −5 V, T_J = 25°C	–	–	18	A
Pulsed Drain−to−Source Diode Forward Current (Note 2)	I_{SDM}	V_{GS} = −5 V, T_J = 25°C	–	–	132	A
Forward Diode Voltage	V_{SD}	V_{GS} = −5 V, I_{SD} = 10 A, T_J = 25°C	–	4	–	V
Reverse Recovery Time	t_{RR}	V_{GS} = −5/20 V, I_{SD} = 20 A, dI_S/dt = 1000 A/μs	–	16	–	ns
Reverse Recovery Charge	Q_{RR}		–	62	–	nC
Reverse Recovery Energy	E_{REC}		–	5	–	μJ
Peak Reverse Recovery Current	I_{RRM}		–	8	–	A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25°C UNLESS OTHERWISE NOTED)




Figure 1. On Region Characteristics




Figure 2. Normalized On−Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On Resistance vs. Junction Temperature




Figure 4. On−Resistance vs. Gate−to−Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source−to−Drain Diode Forward Voltage vs. Source Current

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25°C UNLESS OTHERWISE NOTED) (CONTINUED)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain−to−Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (T_J = 25°C UNLESS OTHERWISE NOTED) (CONTINUED)






Figure 13. Junction−to−Case Transient Thermal Response Curve

Downloaded from Arrow.com.

TO−247−3LD
CASE 340CX
ISSUE A

DATE 06 JUL 2020





NOTES: UNLESS OTHERWISE SPECIFIED.

A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.20	2.40	2.60
A2	1.40	1.50	1.60
D	20.32	20.57	20.82
E	15.37	15.62	15.87
E2	4.96	5.08	5.20
e	~	5.56	~
L	19.75	20.00	20.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
Q	5.34	5.46	5.58
S	5.34	5.46	5.58
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D1	13.08	~	~
D2	0.51	0.93	1.35
E1	12.81	~	~
ØP1	6.60	6.80	7.00

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON93302G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−247−3LD**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.