


LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

PCB terminal with proven clamping yoke connection at 5.00 and 5.08 mm pitch. Conductor outlet direction 90°, 135° and 180°. Suitable for conductor cross-sections up to 2.5 mm².

General ordering data

Version	Printed circuit board terminals, 5.08 mm, Number of poles: 3, 90°, Solder pin length (l): 3.5 mm, tinned, black, Clamping yoke connection, Clamping range, max. : 2.5 mm ² , Box
Order No.	1716030000
Type	LM 5.08/03/90 3.5SN BK BX
GTIN (EAN)	4008190365325
Qty.	114 ST
Product data	IEC: 630 V / 17.5 A / 0.2 - 2.5 mm ² UL: 300 V / 15 A / AWG 24 - AWG 14
Packaging	Box

LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693

Dimensions and weights

Depth	10 mm	Depth (inches)	0.3937 inch
Height	17.3 mm	Height (inches)	0.6811 inch
Height of lowest version	13.8 mm	Width	15.79 mm
Width (inches)	0.6217 inch	Net weight	3.2 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

System parameters

Product family	OMNIMATE Signal - series LM	Wire connection method	Clamping yoke connection
Mounting onto the PCB	THT solder connection	Conductor outlet direction	90°
Pitch in mm (P)	5.08 mm	Pitch in inches (P)	0.200 "
Number of poles	3	Pin series quantity	1
Fitted by customer	Yes	Number of rows	1
Max. adjacent poles per row	24	Solder pin length (l)	3.5 mm
Solder pin dimensions	0.95 x 0.8 mm	Solder eyelet hole diameter (D)	1.3 mm
Solder eyelet hole diameter tolerance (D)+ 0.1 mm		Number of solder pins per pole	1
Screwdriver blade	0.6 x 3.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.4 Nm	Tightening torque, max.	0.5 Nm
Clamping screw	M 2.5	Stripping length	6 mm
L1 in mm	10.16 mm	L1 in inches	0.400 "
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Protection degree	IP20	Volume resistance	1.20 mΩ

Material data

Insulating material	Wemid (PA)	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	I
Comparative Tracking Index (CTI)	≥ 600	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy
Contact surface	tinned	Coating	1-3 µm Ni, 4-6 µm SN
Tinning type	matt	Layer structure of solder connection	1...3 µm Ni / 4...6 µm Sn matt
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	120 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	120 °C

Conductors suitable for connection

Clamping range, min.	0.2 mm ²
----------------------	---------------------

LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Clamping range, max.	2.5 mm ²																																																								
Wire connection cross section AWG, min.	AWG 24																																																								
Wire connection cross section AWG, max.	AWG 14																																																								
Solid, min. H05(07) V-U	0.2 mm ²																																																								
Solid, max. H05(07) V-U	2.5 mm ²																																																								
Flexible, min. H05(07) V-K	0.2 mm ²																																																								
Flexible, max. H05(07) V-K	2.5 mm ²																																																								
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.25 mm ²																																																								
w. plastic collar ferrule, DIN 46228 pt 4, max.	1.5 mm ²																																																								
w. wire end ferrule, DIN 46228 pt 1, min.	0.25 mm ²																																																								
w. wire end ferrule, DIN 46228 pt 1, max.	1.5 mm ²																																																								
Plug gauge in accordance with EN 60999 a x b; ø	2.4 mm x 1.5 mm; 1.9mm																																																								
Clampable conductor	<table border="1"> <tr> <td>Cross-section for conductor connection</td> <td>Type fine-wired</td> </tr> <tr> <td></td> <td>nominal 0.5 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length nominal 8 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.5/12 OR</td> </tr> <tr> <td></td> <td>Stripping length nominal 6 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.5/6</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type fine-wired</td> </tr> <tr> <td></td> <td>nominal 0.75 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length nominal 8 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.75/12 W</td> </tr> <tr> <td></td> <td>Stripping length nominal 6 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.75/6</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type fine-wired</td> </tr> <tr> <td></td> <td>nominal 1 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length nominal 8 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H1.0/12 GE</td> </tr> <tr> <td></td> <td>Stripping length nominal 6 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H1.0/6</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type fine-wired</td> </tr> <tr> <td></td> <td>nominal 0.25 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length nominal 8 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.25/10 HBL</td> </tr> <tr> <td></td> <td>Stripping length nominal 5 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.25/5</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>Type fine-wired</td> </tr> <tr> <td></td> <td>nominal 0.34 mm²</td> </tr> <tr> <td>wire end ferrule</td> <td>Stripping length nominal 8 mm</td> </tr> <tr> <td></td> <td>Recommended wire-end ferrule H0.34/10 TK</td> </tr> </table>	Cross-section for conductor connection	Type fine-wired		nominal 0.5 mm ²	wire end ferrule	Stripping length nominal 8 mm		Recommended wire-end ferrule H0.5/12 OR		Stripping length nominal 6 mm		Recommended wire-end ferrule H0.5/6	Cross-section for conductor connection	Type fine-wired		nominal 0.75 mm ²	wire end ferrule	Stripping length nominal 8 mm		Recommended wire-end ferrule H0.75/12 W		Stripping length nominal 6 mm		Recommended wire-end ferrule H0.75/6	Cross-section for conductor connection	Type fine-wired		nominal 1 mm ²	wire end ferrule	Stripping length nominal 8 mm		Recommended wire-end ferrule H1.0/12 GE		Stripping length nominal 6 mm		Recommended wire-end ferrule H1.0/6	Cross-section for conductor connection	Type fine-wired		nominal 0.25 mm ²	wire end ferrule	Stripping length nominal 8 mm		Recommended wire-end ferrule H0.25/10 HBL		Stripping length nominal 5 mm		Recommended wire-end ferrule H0.25/5	Cross-section for conductor connection	Type fine-wired		nominal 0.34 mm ²	wire end ferrule	Stripping length nominal 8 mm		Recommended wire-end ferrule H0.34/10 TK
Cross-section for conductor connection	Type fine-wired																																																								
	nominal 0.5 mm ²																																																								
wire end ferrule	Stripping length nominal 8 mm																																																								
	Recommended wire-end ferrule H0.5/12 OR																																																								
	Stripping length nominal 6 mm																																																								
	Recommended wire-end ferrule H0.5/6																																																								
Cross-section for conductor connection	Type fine-wired																																																								
	nominal 0.75 mm ²																																																								
wire end ferrule	Stripping length nominal 8 mm																																																								
	Recommended wire-end ferrule H0.75/12 W																																																								
	Stripping length nominal 6 mm																																																								
	Recommended wire-end ferrule H0.75/6																																																								
Cross-section for conductor connection	Type fine-wired																																																								
	nominal 1 mm ²																																																								
wire end ferrule	Stripping length nominal 8 mm																																																								
	Recommended wire-end ferrule H1.0/12 GE																																																								
	Stripping length nominal 6 mm																																																								
	Recommended wire-end ferrule H1.0/6																																																								
Cross-section for conductor connection	Type fine-wired																																																								
	nominal 0.25 mm ²																																																								
wire end ferrule	Stripping length nominal 8 mm																																																								
	Recommended wire-end ferrule H0.25/10 HBL																																																								
	Stripping length nominal 5 mm																																																								
	Recommended wire-end ferrule H0.25/5																																																								
Cross-section for conductor connection	Type fine-wired																																																								
	nominal 0.34 mm ²																																																								
wire end ferrule	Stripping length nominal 8 mm																																																								
	Recommended wire-end ferrule H0.34/10 TK																																																								
Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage.. The outside diameter of the plastic collar should not be larger than the pitch (P)																																																								

LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	17.5 A
Rated current, max. number of poles (Tu=20°C)	16 A	Rated current, min. number of poles (Tu=40°C)	17.5 A
Rated current, max. number of poles (Tu=40°C)	14.2 A	Rated voltage for surge voltage class / pollution degree II/2	630 V
Rated voltage for surge voltage class / pollution degree III/2	320 V	Rated voltage for surge voltage class / pollution degree III/3	250 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV	Rated impulse voltage for surge voltage class/ pollution degree III/2	4 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	4 kV	Short-time withstand current resistance	3 x 1s with 120 A

Rated data acc. to CSA

Institute (CSA)	CSA	Certificate No. (CSA)	200039-1815154
Rated voltage (Use group B / CSA)	300 V	Rated voltage (Use group D / CSA)	300 V
Rated current (Use group B / CSA)	18 A	Rated current (Use group D / CSA)	10 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 14
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Rated data acc. to UL 1059

Institute (cURus)	CURUS	Certificate No. (cURus)	E60693
Rated voltage (Use group B / UL 1059)	300 V	Rated voltage (Use group D / UL 1059)	300 V
Rated current (Use group B / UL 1059)	15 A	Rated current (Use group D / UL 1059)	10 A
Wire cross-section, AWG, min.	AWG 24	Wire cross-section, AWG, max.	AWG 14
Reference to approval values	Specifications are maximum values, details - see approval certificate.		

Packing

Packaging	Box	VPE length	348.00 mm
VPE width	134.00 mm	VPE height	30.00 mm

Type tests

Test: Durability of markings	Standard	DIN EN 60512-1-1 / 01.03
	Test	mark of origin, type identification, pitch, type of material, approval marking UL, approval marking CSA, durability
	Evaluation	available
Test: Clampable cross section	Standard	DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02
	Conductor type	Type of conductor solid 0.2 mm ² and conductor cross-section
		Type of conductor stranded 0.2 mm ² and conductor cross-section
		Type of conductor stranded 1.5 mm ² and conductor cross-section
		Type of conductor solid 2.5 mm ² and conductor cross-section

LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Test for damage to and accidental loosening of conductors	Type of conductor and conductor cross-section	AWG 24/1
	Type of conductor and conductor cross-section	AWG 24/19
	Type of conductor and conductor cross-section	AWG 14/1
	Type of conductor and conductor cross-section	AWG 14/19
	Evaluation	passed
	Standard	DIN EN 60999-1 section 9.4 / 12.00
	Requirement	0.2 kg
	Conductor type	Type of conductor and conductor cross-section stranded 0.25 mm ²
	Type of conductor and conductor cross-section	AWG 24/1
	Type of conductor and conductor cross-section	AWG 24/19
Pull-out test	Evaluation	passed
	Requirement	0.3 kg
	Conductor type	Type of conductor and conductor cross-section solid 0.5 mm ²
	Evaluation	passed
	Requirement	0.4 kg
	Conductor type	Type of conductor and conductor cross-section stranded 1.5 mm ²
	Evaluation	passed
	Requirement	0.7 kg
	Conductor type	Type of conductor and conductor cross-section solid 2.5 mm ²
	Type of conductor and conductor cross-section	AWG 14/1
	Type of conductor and conductor cross-section	AWG 14/19
	Evaluation	passed
	Standard	DIN EN 60999-1 section 9.5 / 12.00
	Requirement	≥20 N
	Conductor type	Type of conductor and conductor cross-section stranded 0.25 mm ²
	Type of conductor and conductor cross-section	AWG 24/1
	Type of conductor and conductor cross-section	AWG 24/19
	Evaluation	passed
	Requirement	≥20 N
	Conductor type	Type of conductor and conductor cross-section H05V-U0.5
	Evaluation	passed

LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Requirement	≥ 40 N	
Conductor type	Type of conductor and conductor cross-section	H07V-K1.5
Evaluation	passed	
Requirement	≥ 50 N	
Conductor type	Type of conductor and conductor cross-section	H07V-U2.5
	Type of conductor and conductor cross-section	AWG 14/1
	Type of conductor and conductor cross-section	AWG 14/19
Evaluation	passed	

Important note

IPC conformity	Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.
Notes	<ul style="list-style-type: none"> Rated current related to rated cross-section & min. No. of poles. Wire end ferrule without plastic collar to DIN 46228/1 Wire end ferrule with plastic collar to DIN 46228/4 The data given under CSA relates to a cUL approval - E60693 P on drawing = pitch Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

Classifications

ETIM 6.0	EC002643	ETIM 7.0	EC002643
ETIM 8.0	EC002643	ETIM 9.0	EC002643
ETIM 10.0	EC002643	ECLASS 9.0	27-44-04-01
ECLASS 9.1	27-44-04-01	ECLASS 10.0	27-44-04-01
ECLASS 11.0	27-46-01-01	ECLASS 12.0	27-46-01-01
ECLASS 13.0	27-46-01-01	ECLASS 14.0	27-46-01-01
ECLASS 15.0	27-46-01-01		


LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings


Product image



Dimensional drawing



Graph




LM 5.08/03/90 3.5SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Slotted screwdriver




VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

General ordering data

Type	SDIS 0.6X3.5X100	Version
Order No.	2749810000	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118897012	thickness (A): 0.6 mm
Qty.	1 ST	
Type	SDS 0.6X3.5X100	Version
Order No.	2749340000	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118895568	thickness (A): 0.6 mm
Qty.	1 ST	

Crosshead screwdriver Phillips



Crosshead screwdriver, Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output to ISO 8764-PH, ChromTop tip, SoftFinish grip

General ordering data

Type	SDK PH0 X 60	Version
Order No.	2749400000	Screwdriver, Blade width (B): 0 mm, 60 mm, Blade thickness (A):
GTIN (EAN)	4050118895629	
Qty.	1 ST	