Part Number : 190170006
Product Description : InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Mylar Tape, Tab 2.79 x 0.81mm
Series Number : 19017
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : AA-2134T



Documents and Resources

Drawings

190170006_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-008-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19017
Description	InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Mylar Tape, Tab 2.79 x 0.81mm
Product Name	InsulKrimp
Type	Standard Quick Disconnect
UPC	800753035713

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Red

Downloaded from Arrow.com.

Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulated	Partial
Insulation	PVC
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	0.386/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	2.79mm
Temperature Range - Operating	-50° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.40mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880048
Mini-Mac Applicator	638850800

Downloaded from Arrow.com.

Downloaded from Arrow.com.