





P.C.B. DIMENSION



Compliance: RohS III (2015/863/EU)

Tolerances:			Date	Name	DRS 61010	
			04/07	dr		
Material	02/21	dr				
Soldering conditions	01/11	dr				
IP rating	07/09	dr			30 11 09	
Operating temperature	11/08	dr				
Coding scheme	02/08	dr				
Temperatures	01/08	dr				
Modifications	Date	Name			Page	
					1/2	

Specifications:

Contact rating:	switching: 150mA, 42V DC non-switching: 200mA, 42V DC
Contact resistance:	80mOhm max.
Insulation resistance:	100MOhm min.
Mechanical life:	10 000 cycles
Operating force:	700gf max.
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Soldering conditions:	pre-heat: max. 120°C, max. 70sec. wave soldering: max. 260°C, max. 10sec.
IP rating:	IP67
Material:	Cover: PA66, white O-ring: silicone, black Actuator: POM, gray PCB: epoxy Base: PA66, black Terminal / contact: phosphor bronze, min. 0.07µm gold plated over min. 0.1µm nickel

		BCD				
		Real coded				
10 P o s i t i o n s	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
	9	●	●			●

Compliance: RohS III (2015/863/EU)

Tolerances:			Date	Name	DRS 61010		
			04/07	dr			
Material	02/21	dr					
Soldering conditions	01/11	dr					
IP rating	07/09	dr					
Operating temperature	11/08	dr	knitter-switch		30 11 09		Page
Coding scheme	02/08	dr					2/2
Temperatures	01/08	dr					
Modifications	Date	Name					