

Router - FL MGUARD GT/GT VPN - 2700198

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Security appliance, 10/100/1000 Mbps, NAT, VPN, advanced firewall, SFP combo ports, functionally extendable with licenses


The figure shows a version of the product

Your advantages

- ✓ Replaceable configuration memory
- ✓ Comprehensive connection options
- ✓ Fast operation by means of configuration and remote maintenance portal
- ✓ Flexible routing
- ✓ Secure remote services (VPN) according to IPsec standard
- ✓ Intelligent stateful inspection firewall
- ✓ Central management tool

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 499668
GTIN	4046356499668
Weight per Piece (excluding packing)	760.000 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Router - FL MGUARD GT/GT VPN - 2700198

Technical data

Dimensions

Width	128 mm
Height	110 mm
Depth	69 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 hPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 hPa ... 108 kPa (3500 m above sea level)

Interfaces

Interface	Ethernet (combo)
No. of ports	2 (Combo ports)
Note on the connection method	Either SFP port or RJ45 port active
Transmission physics	Copper or SFP module
Transmission speed	10/100/1000 Mbps (SFP module: 100/1000 Mbps)
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
Interface	Fiber optic interface
Transmission physics	Depending on the SFP module
Transmission speed	1000 Mbps (full duplex)
Transmission length	up to 80 km (Depending on the fiber/SFP module used)
Interface	Serial (RS-232)
Connection method	RS-232-C, 6-pos. MINI-DIN socket (PS/2)

Function

Basic functions	Router with intelligent firewall and Gigabit connectivity and VPN
Status and diagnostic indicators	LEDs: LNK, Mode, Inf, ACT, SPD, FD, US1, US2, Fail, and 7-segment display
Signal contact control voltage	24 V DC (typical)
Signal contact control current	270 mA (typical)

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server

Router - FL MGUARD GT/GT VPN - 2700198

Technical data

Security functions

Virtual private network (VPN) throughput	max. 106 Mbps (Router mode, VPN bidirectional throughput)
	max. 66 Mbps (Stealth mode, VPN bidirectional throughput)
VPN in stealth mode	Supported
Number of VPN tunnels	10 (up to 250 tunnels with additional license as an option)
Dynamic DNS VPN support	Supported
1:1 Network Address Translation (NAT) in the VPN	Supported
Encryption methods	DES, 3DES, AES-128, -192, -256
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
IPsec L2TP server	Supported
IPsec NAT traversal	Supported
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Internet key exchange (IKE)	Quick mode, Main mode, PFS
Dead peer detection (DPD)	to RFC 3706
Firewall data throughput	max. 417 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 174 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	Standard routing, NAT, 1:1-NAT, port forwarding

Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{pp} (within the permitted voltage range)
Supply voltage range	18 V DC ... 32 V DC
Typical current consumption	270 mA (at U _S = 24 V DC)
Max. current consumption	270 mA

General

Mounting type	DIN rail
Type AX	Stand-alone
Net weight	829.5 g
Housing material	Metal

Conformity with EMC directives

Router - FL MGUARD GT/GT VPN - 2700198

Technical data

Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6-2
Test standard	IEC 61000-4-2 (ESD)
Test result	6 kV contact discharge, 8 kV air discharge
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	10 V/m (80 MHz ... 2000 MHz)
Test standard	IEC 61000-4-4 (burst)
Test result	2 kV power line, 1kV data line
Test standard	IEC 61000-4-5 (surge)
Test result	power line: 2 kV (line/earth), 1 kV (line/line), 1kV data line
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	3 V (10 kHz ... 150 kHz), 10 V (150 kHz ... 80 MHz)

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 10 Hz ... 150 Hz, in accordance with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification
Shock	DIN EN 60068-2-27
Vibration (operation)	in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19170406
eCl@ss 11.0	19170406
eCl@ss 4.0	27240400
eCl@ss 4.1	27240400
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170103
eCl@ss 9.0	19170103

Router - FL MGUARD GT/GT VPN - 2700198

Classifications

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC001478
ETIM 6.0	EC001478
ETIM 7.0	EC001478

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	43222609
UNSPSC 18.0	43222609
UNSPSC 19.0	43222609
UNSPSC 20.0	43222609
UNSPSC 21.0	43222609

Approvals

Approvals

Approvals

BV / GL / LR / GL-SW / ABS / RINA / UL Listed / cUL Listed / DNV GL / EAC / GL / cULus Listed

Ex Approvals









Approval details

BV		http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials	42674/B0 BV
----	---	---	-------------

GL		https://approvalfinder.dnvgl.com/	19910-11 HH
----	---	---	-------------

Router - FL MGUARD GT/GT VPN - 2700198

Approvals

LR		http://www.lr.org/en	08/20033
GL-SW			19910-11 HH
ABS		http://www.eagle.org/eagleExternalPortalWEB/	17-HG1621873-PDA
RINA		http://www.rina.org/en	ELE001320XG
UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
DNV GL		https://approvalfinder.dnvgl.com/	TAA00002CU
EAC			RU*DE*08.B.00731/19
GL			
cULus Listed			

Accessories

Accessories

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

Configuration memory

Configuration memory - FL MEM PLUG - 2891259



Exchangeable configuration memory of the device settings for simple device exchange and set-up

Data plug

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

Device parameterization

Software - FL MGUARD DM UNLIMITED - 2981974



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

License

License - FL MGUARD LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGUARD field devices.

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

License - FL MGUARD LIC CIM - 2701083



License for activating CIFS Integrity Monitoring (CIM) on an FL MGUARD

License - FL MGUARD LIC VPN-250 GROUP - 2700192



License for up to 250 additional VPN online connections

License - FL MGUARD LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

License - FL MGUARD LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3 m

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Remote control software

Router - FL MGUARD GT/GT VPN - 2700198

Accessories

License - MGUARD SECURE VPN CLIENT LIC - 2702579



License for mGuard Secure VPN Client v11.x

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>