




55FB1534-24-FLT3-OCS2173 Product Details

[Share](#) [Print](#) [Email](#)


55FB1534-24-FLT3-OCS2173

Spec 44, Spec 55 and Spec RCW Wire and Cable

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Cable Type = Spec 55F
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 24 AWG
- Voltage Rating = 600 VAC

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 147339-000

[Active](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [THREE CONDUCTOR CABLE, SHIELDED, JACKETED, FILTER LI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Cable Type](#) = Spec 55F
- [Cable Style](#) = Primary
- Number of Conductors = 3
- Shield Material = Tin-Plated Copper

Electrical Characteristics:

- Voltage Rating (VAC) = 600

Body Features:

- Wire Size (AWG/CM) = 24 AWG
- Cable Jacket Color = Black, Violet/Violet with Stripe Components
- Conductor Type = Silver-Plated Copper
- Wire Color = Violet/Violet with Striped Components
- Nominal Outside Diameter (mm [in]) = 2.13 [0.084]
- Shield Size = 38 AWG

Industry Standards:

- Government/Industry Qualification = Yes
- Government/Industry Part Number = M85485/12-24U3A
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = 150

Operation/Application:

- Application = General Purpose - Lightweight

Packaging Features:

- Wire Source = United States

Other:

- Brand = Raychem
- Comment = Internal wire size 24 AWG meets or exceeds all requirements of SAE AS85485/10, less identification.; Product meets or exceeds all requirements of SAE AS85485/12 for 24 AWG, less identification.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

