

SIGN	DATE	DESCRIPTION	APPROVER
△	04`20/10	Add the tolerance table	Tason
△	10/19`10	Add the "cUL"	Tason
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item ② Terminal screw: Steel Zinc plating "--" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

Electrical Δ UL/CUL

- Voltage rating: 125VAC/125V
- Current rating: 10A/10A
- Wire range:
- Solid wire(AWG): 16-26/16-26
- Stranded wire(AWG): 16-26/16-16
- Torque(Lb-In): 1.7/1.7
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.25KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:  

T5 xx 01 x 0 xxxx G




02	2 CONTACTS	COLOR	0000: "@ " Logo	RoHS
03	3 CONTACTS	0 Black (RAL9005)	000A: "ANYTEK" Logo	Pb<40,000ppm
...	...	5 Green(RAL6018/T)	Any special item by	
24	24 CONTACTS	6 Blue (RAL5015/A)	customer request.	
		8 Grey(RAL7035/D)	please contact sales	
			department.	

N = Number of poles

Dim A= (N-1) X3.5

Dim B= Nx3.5 Δ

	Dim A	Dim B
2P	±0.10	±0.10
3-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40




P.C.B. LAYOUT

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	T5-3.5mm Series								
PART NO.	T5xx01x0xxxxG				DWG NO.	8T50001			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Tason 2010.10.19	Tason 2010.04.20					UNIT: mm	X. ±0.50
					SCALE: NONE		X.X ±0.30		
				SHEET: 01/01	REV.: F		X.XX ±0.10		
							X° ±1°		

SHEET: 01/01

REV.: F