

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, Black, 1991H x 700W x 1070D mm

AR3130

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Height	199.1 cm
Width	70 cm
Depth	107 cm
Product weight	137.84 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	91.49 cm
minimum mounting depth	26.19 cm
Rack width	19"
Permanent permissible load	1020.6 kg dynamic 1701.0 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	221.6 cm
Package 1 Width	121.9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	99.9 cm
Package 1 Weight	160 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	485

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes

Image of product / Alternate images

Alternative









