


39000320000 - 390 Series



Series: 390

Questions? Contact Littelfuse Support

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog
[Read Now](#)

Accelerate Your Design...from Concept to Completion
Protecting Technology. Protecting Life.

Electronics News and Information

Electrical Characteristics	Technical Resources
Property (Mouseover for details)	Value
Ampere Rating (A)	0.032
Nominal Melting I ² T (A ² sec)	0.0001
MinOperatingTemp	-40
MaxOperatingTemp	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	0.1
Nominal Voltage Drop (mV)	500
Nominal Cold Resistance (Ohms)	8.084
Package Size	TE5 (8.5x8mm)
VAC (V)	125
VDC (V)	125

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email **Submit**

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

- About Littelfuse
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Website Feedback

- Explore Littelfuse
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents