


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2010
© COPYRIGHT 2010 Tyco Electronics AMP GmbH ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	25NOV2017	JL	IY
	A1	ECR-2008102	03AUG2020	ST	EJ










1:1



A1	25/35/50MM2	180°C	850V APPLICATION:ENGRAVING OF LETTER"X1"	34	12	Ag	CuNiSi	1	2	HV 8mm SPRING	A	1-2328073-2
						Ag	Cu	1	1	DEEP DRAWN SOCKET 90 DEGREES		
	25/35/50MM2	180 °C	650V APPLICATIONS:"PUNCH"	37	15	Ag	CuNiSi	1	2	HV 8mm SPRING	A	2328073-2
						Ag	Cu	1	1	DEEP DRAWN SOCKET 90 DEGREES		
	WIRE RANGE	LIMIT TEMPERATURE	MARKING 5	B	A±0.5	UPPER PLATING	MATERIAL	QTY	ITEM	DESCRIPTION	REV	ASSY NO.
				DIMENSIONS								

NOTES

1 PACKAGING: LOOSE PIECE

2 DETAILS OF THE DESIGN REMAIN THE MANUFACTURER RESERVED

3 SPRING IS LUBRICATED

A1 4 APPLICABLE PRODUCT SPECIFICATION AND APPLICATION SPECIFICATION REFER TO 108-94256 AND 114-94083

5 MARKING

TOLERANCING ISO 8015

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.4
1 PLC ±0.1
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL -

FINISH -

DWN J.LI 24NOV2017
CHK E.JIANG 24NOV2017
APVD I.YIN 24NOV2017
PRODUCT SPEC - 4
APPLICATION SPEC - 4
WEIGHT (20 g)

TE Connectivity

NAME HV 8mm, DEEP DRAWN SOCKET 90 DEG. ASSEMBLY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2328073	

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV A1

1470-19 (3/13)

Downloaded from Arrow.com.