



Intel® SSD DC S3710 Series

(1.2TB, 2.5in SATA 6Gb/s, 20nm, MLC)

Specifications

Essentials

Package Specifications

Advanced Technologies

Compatible Products

Ordering / sSpecs / Steppings

Download Drivers

Specifications

Essentials

Status	Launched
Launch Date	Q1'15
Sequential Read	550 MB/s
Sequential Write	520 MB/s
Random Read (100% Span)	85000 IOPS
Random Write (100% Span)	45000 IOPS
Latency - Read	55 µs
Latency - Write	66 µs
Power - Active	6.9W
Power - Idle	0.6W
Vibration - Operating	2.17 GRMS (5-700HZ)
Vibration - Non-Operating	3.13 GRMS (5-800Hz)
Shock (Operating and Non-Operating)	1000 G/0.5ms
Operating Temperature Range	0°C to 70°C
Weight	94 grams
Endurance Rating (Lifetime Writes)	24.3PB
Mean Time Between Failures (MTBF)	2,000,000 hrs
Uncorrectable Bit Error Rate (UBER)	10^17
Warranty Period	5 yrs
Datasheet	Link
Product Brief	Link
Recommended Customer Price	N/A

Package Specifications

Capacity	1200 GB
Form Factor	2.5" 7mm
Interface	SATA 3.0 6Gb/S
Lithography Type	20 nm

Advanced Technologies

Enhanced Power Loss Data Protection	Yes
Hardware Encryption	AES 256 bit
High Endurance Technology (HET)	Yes
Temperature Monitoring and Logging	Yes
End-to-End Data Protection	Yes

Compare +

Related Products

- Data Center SSDs
- Intel® SSD DC S3710 Series
- Products formerly Haleyville

Quick Links

- [Export Full Specifications >](#)
- [Support Overview >](#)
- [Search Distributors >](#)

PCN/MDDS Information

937747: PCN | MDDS
937748: PCN | MDDS

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

"Intel classifications" consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company may be the exporter of record, and as such, your company is responsible for determining the correct classification of any item at the time of export.

Refer to Datasheet for formal definitions of product properties and features.

*Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers, typically represent 1,000-unit purchase quantities, and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. If sold in bulk, price represents individual unit. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

📧 Send us your feedback!

🌐 USA (English)



- Company Information
- Our Commitment
- Communities
- Investor Relations
- Contact Us
- Newsroom
- Jobs

