





P/N FLA-4141-30 SHOWN ON THIS SHEET

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
K	PRODUCT DWG - REV PER EAR 15012	SEP09/21	M.P.
L	PRODUCT DWG - REV PER EAR 15125	JUN28/22	S.M.



ORDERING CODE:



CONSULT WITH AMPHENOL CANADA FOR OTHER OPTIONS NOT LISTED OR SPECIAL REQUESTS.

NOTES:

- MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU & AMENDMENTS.
 - HOUSING: ENGINEERING THERMOPLASTIC, UL FLAMMABILITY RATING 94V-0, COLOUR BLACK
 - POWER CONTACT: COPPER ALLOY, PLATED WITH TIN OVER NICKEL
 - DIMMABLE CONTACT: COPPER ALLOY, PLATED WITH 0.76µm (30µ") GOLD OVER 1.27µm (50µ") NICKEL, DRY LUBRICANT APPLIED TO CONTACT SURFACE AFTER PLATING.
 - POWER CONTACT WIRE: COPPER WITH PVC INSULATION, 14 OR 16 AWG
 - DIMMABLE CONTACT WIRE: COPPER WITH PVC INSULATION, 18 AWG
 - GASKET: EPDM OR SILICONE RUBBER, WHEN APPLICABLE
- ELECTRICAL CHARACTERISTICS:
 - POWER CONTACTS:
 - CURRENT RATING: 15 A MAX
 - VOLTAGE RATING: 480 VAC/DC
 - DIMMING CONTACTS:
 - CURRENT RATING: 1.5 A MAX
 - VOLTAGE RATING: 30 VAC/DC
- SPECIFICATIONS:
 - ANSI C136-41-2021
 - ANSI C136-10-2017
 - UL 773



UNLESS SPECIFIED OTHERWISE		DRAWN	B.COOPING	MAR13/19
PRIMARY UNITS	MILLIMETERS	CHECKED	S.MUGAN	MAR13/19
SECONDARY UNITS	INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES		O.A. APP'D		
GENERAL TOLERANCES		DWG APPR.		
1 DECIMAL PLACE	±0.3	ENG. REL. NO.		
2 DECIMAL PLACES		REF.		
3 DECIMAL PLACES		THIRD ANGLE PROJECTION		
ANGULAR DEGREES		DO NOT SCALE DRAWING		

Amphenol Canada Corp.
Commercial Products


FLA SERIES, NEMA / ANSI C136.41,
DIMMING CONTROL RECEPTACLE,
FIXED, RoHS COMPLIANT

P-FLA-XXXX-XX-XX

CODE ID NO. 03554 | DWG SIZE: X | SCALE: 2:1 | SHEET 1 OF 2


THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
K	PRODUCT DWG - REV PER EAR 15012	SEP09/21	M.P.
L	PRODUCT DWG - REV PER EAR 15125	JUN28/22	S.M.




RECOMMENDED PANEL CUTOUT
OUTSIDE VIEW OF PANEL

HOUSING



PANEL GASKET
SEE ORDERING CODE



UNLESS SPECIFIED OTHERWISE	DRAWN	B.COPPING	MAR13/19
PRIMARY UNITS MILLIMETERS	CHECKED	S.MUGAN	MAR13/19
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE ±0.3	ENG. REL. NO.		
2 DECIMAL PLACES	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

Amphenol Canada Corp.
Commercial Products

FLA SERIES, NEMA / ANSI C136.41,
DIMMING CONTROL RECEPTACLE,
FIXED, RoHS COMPLIANT

P-FLA-XXXX-XX-XX

DWG. NO.	REV
	L
CODE ID NO. 03554	DWG SIZE: X
SCALE: 2:1	SHEET 2 OF 2